

SPECIFICATION SHEET

Item Number 0110000

Saf-T-Brace®

For Retrofit or New Construction Applications

No Attic Access Required

Specifications

- Provides fast fingertip expansion and positive attachment to joists
- · Teeth twist and lock into joist to create more secure connection
- Magnet secures box to hanger bar for hands-free installation
- Fits 16" to 24" ceiling joists
- Fits all ceiling fans
- · For Fixture support of 150 lbs. or less on 16" centers
- For Fixture support of 50 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less
- Position box anywhere along the brace
- Heavy duty, all metal, dual mount* electrical box
- 1-1/2" box depth, 15.5 cubic inch wiring capacity
- Six 1/2" Romex® or conduit knockouts; 1 Romex® connector
- Includes Saf-T-Cap® to protect inner workings during drywall installation
- · Includes mounting hardware and instructions

Pack Information

Individually Packaged

• 24 Per Cut Case







Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC* Safety Codes.

 * Dual Mount = Box is threaded for #8-32 (ideal for box covers and lightweight fixtures) and #10-24 screws (ideal for heavier fixtures and ceiling fans).

Romex® is a registered trademark of Southwire Company.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

(W), WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.