

Item Number **0140000**

Saf-T-Brace®

For Retrofit or New Construction Applications

No Attic Access Required

Specifications

- Provides fast fingertip expansion and positive attachment to joists
- Teeth twist and lock into joist to create more secure connection
- Magnet secures box to hanger bar for hands-free installation
- Larger box for increased wiring capacity
- Fits 16" to 24" ceiling joists
- Fits all ceiling fans
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 50 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less
- Position box anywhere along the brace
- Heavy duty, all metal, dual mount* electrical box
- 2-1/8" box depth, 21.5 cubic inch wiring capacity
- Six 1/2" Romex® or conduit knockouts; 1 Romex® connector
- Includes Saf-T-Cap® to protect inner workings during drywall installation or painting
- Includes mounting hardware and instructions



Pack Information

- Individually Packaged
- 12 Per Cut Case



85E6

Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC® Safety Codes.

* Dual Mount = Box is threaded for #8-32 (ideal for box covers and lightweight fixtures) and #10-24 screws (ideal for heavier fixtures and ceiling fans).

Romex® is a registered trademark of Southwire Company.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.