

Item Number 6113900

Dimmable LED Wall Fixture Textured White
Finish White Glass Lens

Specifications

- Height: 7.75"
- Diameter: 7.75"
- Extends: 4.00"
- Back Plate: D: 7.75"
- Includes 12 Watt Integrated LED
- Hours: 50000
- Life (years)*: 45.6
- Fixture Lumens: 1100
- Color Temperature (Kelvin): 3000
- Equivalent Incandescent Wattage: 75W
- Color Designation: Warm White


**Installation**

Refer to instruction manual for installation and additional warnings.
Consult a qualified electrician if unsure how to proceed.

Warranty Information - 5 Year Limited Warranty

This Westinghouse Lighting Fixture is warranted against defects in material and workmanship for a period of Five Years from purchase date.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 and Westinghouse are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

Item Number 6113900**Compatible Dimmers**

Manufacturer	Series/Model
Leviton	DDL06-1LZ, C22-6672-1LW, 06674-002-10W, IPL06-011-10Z, RDL-001-10Z, RNL06-001-10Z, TSL06
Lutron	DVCL-153P, MACL-153M, PD-6WCL, MRF2-6CL, SCL-153P, DVCL-253P, CTCL-153P, PD-10NXD

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

® and Westinghouse are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.