

Item Number 7207800

Cayuga Ceiling Fan

60 in. Oil Rubbed Bronze Finish
Reversible Blades (Applewood/Cherry) Opal Frosted Glass

Specifications

Size	60"
Blades	Reversible Plywood Blades (Applewood/Cherry)
Blade Pitch	11°
Approved Location	Indoor
Suggested Room Size	Great Room (up to 20x20)
Down Rod	3/4" x 6"
Installation	Down Rod Only
Max. Ceiling Angle	N/A
Lead Wire	54"
Light Bulb Usage	Includes (2) Medium (E26) Base, 8 Watt T7 LED Lamps
Control	Remote Control Included
Motor Finish	Oil Rubbed Bronze
Motor Material	Silicon Steel Motor 188mm x 22mm
Reverse Airflow	Yes
Capacitor	Dual
Switch Housing Cap	Not Included



Reversible Cherry
Finish Blades

Energy Information


	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	6098	N/A
Energy Use (excludes lights) ^Δ	57	N/A
Airflow (CFM) ^Δ	4420	N/A
Airflow Efficiency (CFM/W) ^Δ	78	N/A
Estimated Yearly Energy Cost ^Δ	\$16	N/A
RPM (High)	145	
Amp (High)	0.68	
Watts (High)	81	



Light Source

Number of Lamps.....	2
Energy Use (Watts) [†]	8
Equiv. Incand. Wattage [†]	60
Light Appearance (Kelvin).....	3000
Lumen [†]	800
CRI.....	80
Average Rated Hours.....	25000
Life in Years ^{**†}	22.80
Estimated Yearly Energy Cost..	\$0.96

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

^Δ Based on typical use, excluding lights
^{*} Based on 12 cents per kWh and 6.4 hours use per day
[†] Values are per lamp
^{**} Based on 3hrs./day

Item Number 7207800

Cayuga Ceiling Fan

60 in. Oil Rubbed Bronze Finish
 Reversible Blades (Applewood/Cherry) Opal Frosted Glass

A. Top of Canopy to Bottom of Blades	13.8"
B. Top of Canopy to Bottom of Switch House	11.5"
C. Top of Canopy to Bottom of Canopy	2.6"
D. Width of Motor Housing.....	10.6"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass.....	17.1"



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
 Used under license by Westinghouse Lighting. All Rights Reserved.