

## Item Number 7209600

## Carolina LED Ceiling Fan

52 in. Oil Rubbed Bronze Finish  
Reversible Blades (Applewood/Cherry) Amber Alabaster Glass

### Specifications

Size .....	52"
Blades .....	Reversible MDF Blades (Applewood/Cherry)
Blade Pitch .....	12°
Approved Location .....	Indoor
Suggested Room Size .....	Large Room (up to 15x15)
Down Rod .....	N/A
Installation .....	Hugger
Max. Ceiling Angle .....	N/A
Lead Wire .....	12"
Light Bulb Usage .....	Includes (2) Medium (E26) Base, 8 Watt T7 LED Lamps
Control .....	Not Adaptable
Motor Finish .....	Oil Rubbed Bronze
Motor Material .....	Silicon Steel Motor 153mm x 17mm
Reverse Airflow .....	Yes
Capacitor .....	Triple
Switch Housing Cap .....	Not Included



Reversible Cherry  
Finish Blades

### Energy Information


	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	N/A	3361
Energy Use (excludes lights) <sup>A</sup> .....	N/A	34
Airflow (CFM) <sup>A</sup> .....	N/A	2480
Airflow Efficiency (CFM/W) <sup>A</sup> .....	N/A	73
Estimated Yearly Energy Cost <sup>A</sup> .....	N/A	\$9
RPM (High) .....	157	
Amp (High) .....	0.44	
Watts (High) .....	52	



### Light Source

Number of Lamps.....	2
Energy Use (Watts) <sup>†</sup> .....	8
Equiv. Incand. Wattage <sup>†</sup> .....	60
Light Appearance (Kelvin).....	3000
Lumen <sup>†</sup> .....	800
CRI.....	80
Average Rated Hours.....	15000
Life in Years <sup>**†</sup> .....	13.60
Estimated Yearly Energy Cost..	\$0.96

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.  
Used under license by Westinghouse Lighting. All Rights Reserved.

<sup>Δ</sup> Based on typical use, excluding lights  
<sup>\*</sup> Based on 12 cents per kWh and 6.4 hours use per day  
<sup>†</sup> Values are per lamp  
<sup>\*\*</sup> Based on 3hrs./day

## Item Number 7209600

## Carolina LED Ceiling Fan

52 in. Oil Rubbed Bronze Finish  
 Reversible Blades (Applewood/Cherry) Amber Alabaster Glass

A. Top of Canopy to Bottom of Blades .....	6.9"
B. Top of Canopy to Bottom of Switch House .....	9.8"
C. Top of Canopy to Bottom of Canopy .....	N/A
D. Width of Motor Housing.....	11.1"
E. Width of Canopy.....	N/A
F. Top of Canopy to Bottom of Glass.....	13.8"




If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.  
 Used under license by Westinghouse Lighting. All Rights Reserved.