

Item Number 7234400

Turbo Swirl Ceiling Fan

30 in. White Finish
White Blades Opal Frosted Glass



Specifications

| | |
|--------------------------|--|
| Size | 30" |
| Blades..... | MDF Blades (White) |
| Blade Pitch..... | 18° |
| Approved Location | Indoor |
| Suggested Room Size..... | Small Room (10x10) or smaller |
| Down Rod..... | 3/4" x 4" |
| Installation..... | Down Rod Only |
| Max. Ceiling Angle..... | 18° |
| Lead Wire | 78" |
| Light Bulb Usage..... | Includes (1) Candelabra (E12) Base, 4.5 Watt G16-1/2 LED Lamp |
| Control..... | Remote Control Adaptable |
| Motor Finish..... | White |
| Motor Material | Silicon Steel Motor 153mm x 15mm |
| Reverse Airflow..... | Yes |
| Capacitor | Triple |
| Switch Housing Cap..... | Not Included |

Energy Information


| | <u>With down rod</u> | <u>Hugger/ Without down rod</u> |
|---|----------------------|-------------------------------------|
| Airflow (CFM) when operated at high speed..... | 2267 | N/A |
| Energy Use (excludes lights) ^Δ | 30 | N/A |
| Airflow (CFM) ^Δ | 1690 | N/A |
| Airflow Efficiency (CFM/W) ^Δ | 57 | N/A |
| Estimated Yearly Energy Cost ^Δ | \$8 | N/A |
| RPM (High) | 227 | |
| Amp (High) | 0.38 | |
| Watts (High) | 45 | |



Light Source

| | |
|---|--------|
| Number of Lamps..... | 1 |
| Energy Use (Watts) [†] | 4.50 |
| Equiv. Incand. Wattage [†] | 60 |
| Light Appearance (Kelvin)..... | 2700 |
| Lumen [†] | 500 |
| CRI..... | 80 |
| Average Rated Hours..... | 15000 |
| Life in Years ^{**†} | 13.60 |
| Estimated Yearly Energy Cost.. | \$0.54 |

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

^Δ Based on typical use, excluding lights
^{*} Based on 12 cents per kWh and 6.4 hours use per day
[†] Values are per lamp
^{**} Based on 3hrs./day

Item Number 7234400

Turbo Swirl Ceiling Fan

30 in. White Finish
White Blades Opal Frosted Glass

| | |
|--|-------|
| A. Top of Canopy to Bottom of Blades | 10" |
| B. Top of Canopy to Bottom of Switch House | 11.5" |
| C. Top of Canopy to Bottom of Canopy | 2.3" |
| D. Width of Motor Housing..... | 7" |
| E. Width of Canopy..... | 5" |
| F. Top of Canopy to Bottom of Glass..... | 14.5" |



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.