

## Item Number 7235900

## Swirl Ceiling Fan

52 in. Brushed Nickel Finish  
Reversible Blades (Rosewood/Light Maple) Frosted Swirl Glass

### Specifications

Size .....	52"
Blades .....	Reversible MDF Blades (Rosewood/Light Maple)
Blade Pitch .....	11°
Approved Location .....	Indoor
Suggested Room Size .....	Large Room (up to 15x15)
Down Rod .....	3/4" x 4"
Installation .....	Combo
Max. Ceiling Angle .....	18°
Lead Wire .....	78"
Light Bulb Usage .....	Includes (4) Candelabra (E12) Base, 4.5 Watt B11 LED Lamps
Control .....	Remote Control Adaptable
Motor Finish .....	Brushed Nickel
Motor Material .....	Cold Rolled Steel Motor 153mm x 15mm
Reverse Airflow .....	Yes
Capacitor .....	Triple
Switch Housing Cap .....	Not Included



Reversible Light Maple  
Finish Blades

### Energy Information


	<u>With down rod</u>	<u>Hugger/ Without down rod</u>
Airflow (CFM) when operated at high speed.....	4771	4259
Energy Use (excludes lights) <sup>A</sup> .....	39	39
Airflow (CFM) <sup>A</sup> .....	3267	2987
Airflow Efficiency (CFM/W) <sup>A</sup> .....	83	76
Estimated Yearly Energy Cost <sup>A</sup> .....	\$11	\$11
RPM (High) .....	185	
Amp (High) .....	0.55	
Watts (High) .....	66	



### Light Source

Number of Lamps.....	4
Energy Use (Watts) <sup>†</sup> .....	4.50
Equiv. Incand. Wattage <sup>†</sup> .....	60
Light Appearance (Kelvin).....	2700
Lumen <sup>†</sup> .....	500
CRI.....	80
Average Rated Hours.....	15000
Life in Years <sup>**†</sup> .....	13.60
Estimated Yearly Energy Cost..	\$0.54

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.  
Used under license by Westinghouse Lighting. All Rights Reserved.

<sup>Δ</sup> Based on typical use, excluding lights  
<sup>\*</sup> Based on 12 cents per kWh and 6.4 hours use per day  
<sup>†</sup> Values are per lamp  
<sup>\*\*</sup> Based on 3hrs./day

## Item Number 7235900

## Swirl Ceiling Fan

52 in. Brushed Nickel Finish  
 Reversible Blades (Rosewood/Light Maple) Frosted Swirl Glass

A. Top of Canopy to Bottom of Blades .....	13.5"
B. Top of Canopy to Bottom of Switch House .....	12"
C. Top of Canopy to Bottom of Canopy .....	2.3"
D. Width of Motor Housing.....	12"
E. Width of Canopy.....	5.3"
F. Top of Canopy to Bottom of Glass.....	18"



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.  
 Used under license by Westinghouse Lighting. All Rights Reserved.