

## Item Number 7305000

## Alloy Ceiling Fan

42 in. Matte Black Finish  
Reversible Blades (Charcoal/Riverbed) Opal Frosted Glass

### Specifications

Size .....	42"
Blades.....	Reversible MDF Blades (Charcoal/Riverbed)
Blade Pitch.....	13°
Approved Location .....	Indoor
Suggested Room Size.....	Small Room (10x10) or smaller
Down Rod.....	3/4 x 4"
Installation.....	Down Rod Only
Max. Ceiling Angle.....	13°
Lead Wire .....	24"
Light Bulb Usage.....	Includes (2) Medium (E26) Base, 8 Watt T7 LED Lamps
Control .....	Remote control adaptable and pull chain included
Motor Finish.....	Matte Black
Motor Material .....	Silicon Steel Motor 153mm x 12mm
Reverse Airflow.....	Yes
Capacitor .....	Dual
Switch Housing Cap.....	Not Included



Reversible Riverbed  
Finish Blades

### Energy Information

	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	2897	N/A
Energy Use (excludes lights) <sup>Δ</sup> .....	42	N/A
Airflow (CFM) <sup>Δ</sup> .....	2176	N/A
Airflow Efficiency (CFM/W) <sup>Δ</sup> .....	51	N/A
Estimated Yearly Energy Cost <sup>Δ</sup> .....	\$12	N/A
RPM (High) .....	214	
Amp (High).....	0.44	
Watts (High).....	53	



### Light Source

Number of Lamps.....	2
Energy Use (Watts) <sup>†</sup> .....	8
Equiv. Incand. Wattage <sup>†</sup> .....	60
Color Temperature (Kelvin).....	3000
Color Designation: Warm White	
Lumen <sup>†</sup> .....	800
CRI.....	80
Average Rated Hours.....	15000
Life in Years <sup>**†</sup> .....	13.60
Estimated Yearly Energy Cost..	\$0.96

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

<sup>Δ</sup> Based on typical use, excluding lights  
<sup>\*</sup> Based on 12 cents per kWh and 6.4 hours use per day  
<sup>†</sup> Values are per lamp  
<sup>\*\*</sup> Based on 3hrs./day

## Item Number 7305000

## Alloy Ceiling Fan

42 in. Matte Black Finish  
 Reversible Blades (Charcoal/Riverbed) Opal Frosted Glass

A. Top of Canopy to Bottom of Blades .....	6.4"
B. Top of Canopy to Bottom of Switch House .....	11"
C. Top of Canopy to Bottom of Canopy .....	2.5"
D. Width of Motor Housing.....	6.8"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass.....	11.8"



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.