

## Item Number 7307100

## Porto Ceiling Fan

52 in. Black-Bronze Finish  
Reversible Blades (Dark Walnut/Wengue) Amber Frosted Glass

### Specifications

Size .....	52"
Blades.....	Reversible Plywood Blades (Dark Walnut/Wengue)
Blade Pitch.....	12°
Approved Location .....	Indoor
Suggested Room Size.....	Large Room (up to 15x15)
Down Rod.....	3/4 x 4"
Installation.....	Combo
Max. Ceiling Angle.....	17°
Lead Wire .....	54"
Light Bulb Usage.....	Includes (1) Medium (E26) Base, 9.8 Watt Omni A19 LED Lamp
Control.....	Remote control adaptable and pull chain included
Motor Finish.....	Black-Bronze
Motor Material .....	Silicon Steel Motor 153mm x 15mm
Reverse Airflow.....	Yes
Capacitor .....	Triple
Switch Housing Cap.....	Not Included



Reversible Wengue  
Finish Blades

### Energy Information

	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	4430	3689
Energy Use (excludes lights) <sup>Δ</sup> .....	38	38
Airflow (CFM) <sup>Δ</sup> .....	3295	2677
Airflow Efficiency (CFM/W) <sup>Δ</sup> .....	87	70
Estimated Yearly Energy Cost <sup>Δ</sup> .....	\$11	\$11
RPM (High) .....	158	
Amp (High) .....	0.50	
Watts (High) .....	60	



### Light Source

Number of Lamps.....	1
Energy Use (Watts) <sup>†</sup> .....	9.80
Equiv. Incand. Wattage <sup>†</sup> .....	60
Color Temperature (Kelvin).....	3000
Color Designation: Warm White	
Lumen <sup>†</sup> .....	800
CRI.....	80
Average Rated Hours.....	15000
Life in Years <sup>**†</sup> .....	13.60
Estimated Yearly Energy Cost..	\$1.18

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

® and Westinghouse are trademarks of Westinghouse Electric Corporation.  
Used under license by Westinghouse Lighting. All Rights Reserved.

<sup>Δ</sup> Based on typical use, excluding lights  
<sup>\*</sup> Based on 12 cents per kWh and 6.4 hours use per day  
<sup>†</sup> Values are per lamp  
<sup>\*\*</sup> Based on 3hrs./day

## Item Number 7307100

## Porto Ceiling Fan

52 in. Black-Bronze Finish  
 Reversible Blades (Dark Walnut/Wengue) Amber Frosted Glass

A. Top of Canopy to Bottom of Blades .....	10.8"
B. Top of Canopy to Bottom of Switch House .....	12.8"
C. Top of Canopy to Bottom of Canopy .....	2.7"
D. Width of Motor Housing.....	7.9"
E. Width of Canopy.....	5.2"
F. Top of Canopy to Bottom of Glass.....	20.1"



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.