

**Item Number 7787300****Dual Slide 4 Speed Ceiling Fan and Incandescent Light Wall Control**

## Specifications

- Height: 4.5"
- Width: 2.75"
- Depth: 0.63"
- No. of Control Speeds: 4
- Max. Fan Amps: 1.25
- Max. Light Watts: 300
- Light Dimmer Type: Full Range

## Features & Benefits

- Four fan speeds (high/medium-high/medium/low)
- Turns any three-speed fan into a four-speed fan
- Full-range sliding light dimmer for incandescent light bulbs
- Requires three-conductor wire installation for use in a standard junction box

## Recommended Uses


- Use to control ceiling fan
- Adjust light levels
- Replace toggle switch or pull chain operation

## Installation

Refer to instruction manual for installation and additional warnings. Consult a qualified electrician if unsure how to proceed.



*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.