

Specification guide

Model: 6203XXXX



NOTE: Items other than the mirror shown in the pictures above are not included

FEATURES

- Energy Efficient and Long-Lasting LED Lighting
- Forward-Facing Lighting with Back Lit
- Smart Touch Control Switch
- Acrylic Light Diffuser
- Built-in 6" Dia. LED Lit Cosmetic Mirror with 3x Power
- 5mm Copper-Free Mirror
- Durable Aluminum Frame
- Surface-Mount with French Cleat Mounting Bracket
- Hardwired (Junction box required)

LIGHTING

- LED (Light-Emitting Diode)
- Average Bulb Life of 50,000 hours
- CRI: 85+
- Dual Color Temperature: 3000K & 6000K
- Compatible with Wall Dimmers
- Brightness & Power Consumption: See Page 2
- Power Requirements: 110-130V AC, 60Hz

SAFETY

- Safety Backed Mirror
- IP44 Rated
- UL Certified

OVERVIEW


innoci-usa does not cut corners and only uses the highest quality components and bulbs to make sure that the mirror will be maintenance free and function like the day you purchased for average 50,000 hours of use. Innoci-usa prides itself on providing unmatched price vs quality for all of our products. All mirrors come with a 5-year limited warranty.

innoci-usa Inc. Newport Beach, CA 92660

www.innoci-usa.com (866) 479-8076

customerservice@innoci-usa.com





Model #	A	В	Brightness (Lumen)	Power Consumption (Watt)
62033636	36	1-3/16"	2745	30.5
62034242	42	1-3/16"	3195	38.5

innoci-usa Inc. Newport Beach, CA 92660 www.innoci-usa.com (866) 479-8076

innociusa

customerservice@innoci-usa.com