

# Specification guide

Model: 6343XXXX



(Items other than the mirror shown in the picture above are not included)

### **FEATURES**

- Energy Efficient and Long-Lasting LED Lighting
- Built-in 5.5" Dia. LED Lit Magnifier with 3x Magnification
- Digital Clock Display
- Dual Switches (Rocker & IR Sensor) for Added Convenience
- Durable Aluminum Frame with Steel Back Panel
- 5mm Copper-Free Mirror
- Surface-Mount with French Cleat
- Hardwired (Junction box required)

#### LIGHTING

- Front-Facing Lighting
- Average Bulb Life of 50,000 hours
- CRI: 85+
- Color Temperature: 6000K (Daylight)
- Dimmable using Built-in IR Sensor\*
- Brightness & Power Consumption: see page 2
- Power Requirements: 110-130V AC, 60Hz

#### **SAFETY**

- Safety Backed Mirror
- IP44 Rated
- UL Listed

#### **OVERVIEW**

**innoci-usa** does not cut corners and only uses the highest quality components and bulbs to make sure that the mirror will be maintenance free and function like the day you purchased for average 50,000 hours of use. **innoci-usa** prides itself on providing unmatched price vs quality for all of our products. All mirrors come with a 5-year limited warranty.


innoci-usa Inc. Santa Fe Springs, CA 90670 www.innoci-usa.com (866) 479-8076

customerservice@innoci-usa.com



<sup>\*</sup> Not compatible with wall dimmer switch.





Model #	A	В	С	Brightness (Lumen)	Power Consumption (Watt)
63434040	40	40	1 5/8	2490	41
63434835	48	35	1 5/8	2580	42
63435636	56	36	1 5/8	2850	46
63436028	60	28	1 5/8	2730	44

## © innoci usa, Inc. All rights reserved.

innoci-usa Inc. Santa Fe Springs, CA 90670 www.innoci-usa.com (866) 479-8076

innociusa

customerservice@innoci-usa.com