

Fire Vulcan® Rechargeable Lantern

Specific lighting needs require specific tools. With the right lighting tool, you can identify potential or existing problems before they interrupt your ability to get the job done. In addition the costs savings of using the right tool over time will benefit your bottom line.

There is a real need to cut costs wherever possible, yet we cannot afford to forget about environmental issues. Streamlight rechargeable lighting tools make good economic environmental sense. Over time they cost significantly less to operate; and they reduce the amount of batteries used, thereby relieving the problem of battery disposal. Therefore you will not only save on the cost of batteries, you'll save the time that's wasted when you discover your light isn't working - and the steps involved in getting and replacing batteries. More powerful and more economical, Streamlight rechargeables pack a lot more power, are more dependable and more cost-efficient

In a smoke-filled room, it's not only important that you can see – it's critical that you can be seen. In addition to the high-intensity halogen lamp, the rechargeable Fire Vulcan has two powerful, ultra-bright LED taillights. Your partners can follow you through the thickest smoke; and they can find you fast in an emergency. The toggle switch makes it easy to go between strobe and steady modes, so you can use it to increase visibility at a fire or accident scene or signal for help.

Case Material: High-impact ABS thermoplastic housing with rubberized cushioned-grip handle.

Dimensions: Length: 7.50 in. (19.05 cm) Width: 5 in. (12.7 cm) Height: 6.50 in. (16.51 cm)

Weight: 3.3 lbs (1.5 kg) with battery

Light Source: High-intensity halogen bi-pin 8 watt spot with 100 hour life time, and (2) two ultra bright Blue LEDs

Light Output: 80,000 candela peak beam intensity 8W spot bi-pin bulb; 150 lumens

Battery/Run Time: Zero-maintenance 4.5 Ah sealed lead-acid battery rechargeable up to 500 times.

Up to 3 hours (Steady Halogen and LEDs)

Up to 6 hours (Blinking Halogen and LEDs)

Up to 60 hours (LEDs only)

Models: Standard System - Includes quick release buckle strap, charging rack and both AC and DC chargers.

Vehicle Mount System - Includes quick release buckle strap and 12 V DC vehicle-mountable direct wire charging rack.

- Approvals**:
- Factory Mutual (FM) approved for Class I, II, III, Division 2.
 - Canadian Standards Association (CSA) certified for Class I, II, Division 2; Class III.
 - Rack meets requirements of NFPA 1901-12-1.7 (1999) mounted in any position.
 - Most models meet applicable European Community Directives and ATEX Zone 2

Warranty: Limited lifetime warranty.



**With battery (included in purchase).
Assembled in USA*

Item	UPC	Part #
Standard System with quick release shoulder strap. AC/12V DC.		
Fire Vulcan Standard System 230V (8WS) Orange	080926-44410-2	44410
Fire Vulcan Standard System 230V (8WF) Orange	080926-44404-1	44412
Fire Vulcan Standard System 230V (3WS/T-4) Orange (ATEX Approved)	080926-44404-1	44404
Fire Vulcan Standard System 240V (3WS/T-4) Orange (ATEX Approved)	080926-44406-5	44406
Fire Vulcan Standard System 240V (8WS) Orange	080926-44404-1	44403
Fire Vulcan Standard System 100V (3WS/T-4) Orange (ATEX Approved)	080926-44407-2	44407
Fire Vulcan Standard System 100V (8WS) Orange	080926-44425-6	44425
Fire Vulcan Standard System 120V (8WS) Orange	080926-44400-3	44400
Vehicle Mount System with quick release shoulder strap. 12V DC.		
Fire Vulcan Vehicle Mount System 12V DC (3WS/T-4) Orange (ATEX Approved)	080926-44405-8	44405
Fire Vulcan Vehicle Mount System 12V DC (8WS) Orange	080926-44401-0	44401
Fire Vulcan Light Only - (8WS) Orange	080926-44411-9	44411
<i>See reverse for additional part numbers</i>		





Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
240V AC charge cord	080926-22241-0	22241
230V AC charge cord	080926-22664-7	22664
100V AC charge cord	080926-22666-1	22666
Battery	080926-44007-4	44007
Quick Release Strap	080926-44050-0	44050
Charging Rack - Orange	080926-44101-9	44101
Direct Wire 12V DC Mounting Rack - Orange	080926-44131-6	44131
Shoulder Strap	080926-45232-9	45232
8 Watt Bi-Pin Bulb (100 Hr)	080926-45901-4	45901

