



TOOL AND BATTERY WARRANTY



Features

12v & 20v MAX* Charger

20v MAX* 3.0 Amp Hours

20v MAX* 1.5 Amp Hours

12v MAX* 1.3 Amp Hours

DCB101 CHARGER CHARGES ALL 12V MAX* AND 20V MAX* BATTERIES

COMING SOON

20v MAX* LITHIUM ION

Tool Warranty

GUARANTEED TOUGH.®

3 YEAR	1 YEAR	90 DAY
LIMITED WARRANTY	FREE SERVICE	MONEY BACK GUARANTEE

Battery Warranty

2 YEAR	FREE SERVICE ON DCB201 BATTERIES	3 YEAR	FREE SERVICE ON DCB200 BATTERIES
---------------	---	---------------	---

dewalt.com

1-800-4 DEWALT

AVAILABLE THROUGH

GRAINGER.®

FOR THE ONES WHO GET IT DONE

20v MAX* LITHIUM ION

20V MAX* POWER. MAXIMUM PERFORMANCE.



dewalt.com/20VMAX

*With respect to 12V, maximum initial battery voltage (measured without a workload) is 12 volts. Nominal voltage is 10.8. With respect to 20V, maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18. Copyright ©2012 DeWALT. The following are examples of trademarks for one or more DeWALT power tools and accessories: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

8SS4644 DCGR20VMAXTRIBR

GUARANTEED TOUGH.®

DCD985L2 Premium 3-Speed Hammerdrill Kit (3.0 Ah)

11A178



- **All-metal 3-Speed Transmission (0-575/0-1,350/0-2,000 RPM)** fast application and long run-time
- **1/2" Metal Ratcheting chuck** with carbide inserts for optimal bit retention and durability
- **LED Light** 20 second delay after trigger release
- **535 Unit Watts Out** max power for drilling / fastening
- **0-9,775/0-22,950/0-34,000 BPM** for a variety of hammer applications

DCD980L2 Premium 3-Speed Drill/Driver Kit (3.0 Ah)

11A177



- **All-metal 3-Speed Transmission (0-575/0-1,350/0-2,000 RPM)** fast application and improved run-time
- **1/2" Metal Ratcheting chuck** with carbide inserts for optimal bit retention and durability
- **LED Light** 20 second delay after trigger release
- **535 Unit Watts Out** max power for drilling / fastening

WHY PREMIUM DRILLS

VERSATILITY

- 3-Speed Transmission to match drilling and fastening applications
- 1/2 metal ratcheting chuck with carbide inserts for optimal bit retention and durability
- Clutch with 22 Torque settings to match a variety of fastening application

PERFORMANCE

- Drills 122 7/8" auger holes into 2x pine using a 3.0 Ah battery on a single charge
- Optimized motor design for long runtime

DURABILITY

- All steel 3-Speed Transmission to last long in heavy duty applications
- Metal gear case



DCD785C2 Compact Hammerdrill Kit (1.5 Ah)

11A172



- **Compact, lightweight** only 3.5 lbs; fits into tight spaces
- **High Speed Transmission (0-600 / 0-2,000 RPM)** ideal for fastening and drilling
- **1/2" Ratcheting Chuck** with carbide inserts for optimal bit retention and durability
- **LED Light** 20 second delay after trigger release
- **0-9,775/0-22,950/0-34,000 BPM** for a variety of hammer applications

DCD780C2 Compact Drill/Driver Kit (1.5 Ah)

11A170



- **Compact, lightweight** 7.5 in. front to back, only 3.4 lbs
- **High Speed Transmission (0-600 / 0-2,000 RPM)** ideal for fastening and drilling
- **1/2" Ratcheting Chuck** optimal bit retention
- **LED Light** 20 second delay after trigger release

WHY COMPACT DRILLS

COMPACT SIZE & WEIGHT

- 7.5 inches front to back
- 3.4 lbs

OPTIMAL FOR DRILLING

- 1/2" ratcheting chuck
- Drills 97 5/8" auger holes into 2x pine using a 1.5 Ah battery on a single charge

OPTIMAL FOR FASTENING

- Clutch with 15 torque settings to match any fastening application
- Sinks 275 3" deck screws into 2x pine using a 1.5 Ah battery on a single charge



DCF885C2 1/4" Impact Driver Kit (1.5 Ah)

11A180



- **Compact, Lightweight** 5.55 in. front to back, only 2.8lbs
- **High Speed and Power** 0-2,800 rpm; 0-1,400 in-lbs of max torque
- **(3) LED Lights** 20 second delay, provides visibility without shadows after trigger release
- **One handed loading** 1/4" hex chuck accepts 1" bit tips
- **Belt Hook Included**

DCF885L2 1/4" Impact Driver Kit (3.0 Ah)

11A181



- **Compact, Lightweight** 5.55 in. front to back, only 3.4 lbs
- **High Speed and Power** 0-2,800 rpm; 0-1,400 in-lbs of max torque
- **(3) LED Lights** 20 second delay, provides visibility without shadows after trigger release
- **One handed loading** 1/4" hex chuck accepts 1" bit tips
- **Belt Hook Included**

WHY IMPACTS

FAST APPLICATION SPEED

- 0-2800 RPM
- 0-1400 in/lbs torque

GREATER CONTROL

- No kickback
- Less stripping

COMPACT SIZE AND WEIGHT

- 5.55 Inches front to back
- 2.8 lbs with 1.5 Ah battery





20V MAX* LITHIUM ION TOOLS



DCK280C2 11A169
20V MAX* Compact Drill/Driver /
Impact Driver Combo Kit (1.5 Ah)



DCK285C2 11A171
20V MAX* Compact Hammerdrill /
Impact Driver Combo Kit (1.5 Ah)



DCK290L2 11A174
20V MAX* Hammerdrill /
Impact Driver Combo Kit (3.0 Ah)



DCK292L2 11A175
20V MAX* Hammerdrill /
Recip Saw Combo Kit (3.0 Ah)



DCK294L3 11A176
20V MAX* Hammerdrill (3.0 Ah) /
12V MAX* Screwdriver Combo Kit



DCK490L2 11A162
20V MAX* 4-Tool Combo Kit (3.0 Ah)



DCK491L2 11A161
20V MAX* 4-Tool Combo Kit (3.0 Ah)



DCK590L2 11A163
20V MAX* 5-Tool Combo Kit (3.0 Ah)

BATTERIES & CHARGERS



DCB200 11A165
20V MAX* 3.0 Ah
Battery Pack



DCB200-2 11A164
20V MAX* 3.0 Ah Battery 2-Pack



DCB201 11A168
20V MAX* 1.5 Ah Battery Pack



DCB201-2 11A167
20V MAX* 1.5 Ah Battery 2-Pack



DCB101 11A157
12V MAX* - 20V MAX*
Battery Charger



DCB119 11A158
12V MAX* - 20V MAX*
Vehicle Battery Charger



20V MAX* LITHIUM ION TOOLS

DCS380L1 11A179 Reciprocating Saw Kit (3.0 Ah)



- 4-Position keyless blade clamp allows for flush cutting; quick blade change
- Speed of cut
1-1/8" stroke length, 0-3,000 SPM

DCS391L1 11A166 6-1/2" Circular Saw Kit (3.0 Ah)



- Speed of cut and power
3,700 RPM; 460 max watts out
- Comfort grip
overmolded rubber handle and design provides better control
- Cut capacity
6-1/2" blade allows for cutting 2x at 90° and 45°

DCL040 11A159 LED Flashlight



- 110 Lumen LED light provides bright white light
- Pivoting head provides light in any direction
- 11 Hours of run-time on a fully charged DCB200 battery pack

DCH213L2 11A160 3-Mode SDS Rotary Hammer Kit (3.0 Ah)



- SHOCKS ACTIVE VIBRATION CONTROL® Significantly reduces vibration and for user comfort and productivity
- 1.7 ft-lbs Impact Energy provides corded power without the cord

DCD740C1 11A173 3/8" Right Angle Drill Kit (1.5 Ah)



- Dual Speed Transmission (0-650 / 0-2,000 RPM) flexibility for drilling or fastening
- Compact Size
4 in. front to back for tight spaces
- Multi-grip Trigger convenient access when in tight spaces

PERFORMANCE

UP TO
57%
FASTER[†]

UP TO
35%
MORE RUNTIME
Per Charge[†]

ERGONOMICS



UP TO
38%
LIGHTER WEIGHT[†]

OPTIMIZED
HANDLE DESIGN
Contoured with slim profile

IDEAL BALANCE

[†]Speed and runtime claims are versus other leading 18 volt lithium ion tools. Weight claim is versus DC9096.

INNOVATIVE FEATURES



ONE-HANDED
LOADING 1/4"
HEX CHUCK



DUAL VOLTAGE
12V MAX* & 20V
MAX* CHARGER



3-LED ILLUMINATION
WITH DELAY



3-SPEED
TRANSMISSION ON
PREMIUM DRILLS

20V MAX* POWER. MAXIMUM PERFORMANCE.



With up to 57% faster application speed and up to 35% greater runtime than leading 18 Volt lithium ion tools, there's no stopping the 20V MAX* system. The speed, power and control are up to almost any job. Available 3.0 Amp Hour (Ah) and 1.5 Ah lithium ion batteries make it a versatile system. And the comfortable design lets you work all day and get more done.

20V MAX* LITHIUM ION SYSTEM



dewalt.com/20VMAX

GUARANTEED TOUGH.®