

3M™ Reusable Escape Only Mouthpiece Respirator 5500 Series
3M™ Disposable Escape Only Mouthpiece Respirator 5600 Series



Emergency Protection for Critical Situations

Designed for emergency escape from industrial accidents involving known chemicals, the 3M™ Escape Only Mouthpiece Respirators provide health and safety professionals a respiratory protection option for their organizations' emergency escape plans. With the incorporation of 3M technologies, these NIOSH-approved single cartridge escape, mouthpiece style respirators provide respiratory protection for emergency escape from atmospheres containing certain levels of acid gases and certain non-oil based particles. Ammonia/methylamine model also available. *(5604 model only)*

Benefits include:

- Replacement cartridge design on reusable model can extend life of facepiece and potentially provide a cost savings.
- Disposable model provides economical option for temporary site personnel.
- In-service and storage shelf life markings help to determine respirator replacement schedule and manage on-site inventory.*
- Clear, resealable bag provides flexibility in respirator inspection and helps protect respirators in dusty and dirty environments.
- Unique combination Acid Gas cartridge with N95 filter availability for certain industrial applications. *(5512 model only)*

*One-year in-service use and five year storage shelf life based upon proper storage and maintenance per user instructions.

To locate a distributor, go to www.3M.com/EscapeRespirator and select “Where to Buy” link.





3M™ Reusable Escape Only Mouthpiece Respirator 5500 Series

Air purifying escape only mouthpiece respirator provides a versatile option with its replacement cartridge design and N95 filter* capability for certain non-oil based particulates.



Part No.	Product Name	Description	Qty/Case
5502	3M™ Reusable Escape Only Mouthpiece Respirator, Acid Gas	NIOSH approved for protection against certain acid gases (Chlorine, Hydrogen Chloride, Sulfur Dioxide, Chlorine Dioxide, or Hydrogen Sulfide)	20 ea/Case
5512	3M™ Reusable Escape Only Mouthpiece Respirator, Acid Gas/N95	NIOSH approved for protection against certain acid gases (Chlorine, Hydrogen Chloride, Sulfur Dioxide, Chlorine Dioxide, or Hydrogen Sulfide) and certain non-oil based particles (N95 filter).	20 ea/Case

*Only 5512 model includes N95 filter for non-oil based particles.



3M™ Replacement Cartridges and Parts

Part No.	Product Name	Description	Qty/Case
5002	3M™ Escape Only Cartridge, Acid Gas	Use with 3M™ Escape Only Mouthpiece Respirators 5500 Series. NIOSH approved against certain acid gases (Chlorine, Hydrogen Chloride, Sulfur Dioxide, Chlorine Dioxide, or Hydrogen Sulfide).	10 boxes (3 cartridges per box)/Case
5012	3M™ Escape Only Cartridge/Filter, Acid Gas/N95	Use with 3M™ Escape Only Mouthpiece Respirators 5500 Series. NIOSH approved against certain acid gases (Chlorine, Hydrogen Chloride, Sulfur Dioxide, Chlorine Dioxide, or Hydrogen Sulfide) and certain non-oil based particles.	10 boxes (3 cartridges per box)/Case
510E	3M™ Escape Only Mouthpiece and Nose Clip	Replacement mouthpiece and nose clip assembly. Use with 3M™ Escape Only Mouthpiece Respirator 5500 Series.	10 ea/Case
513E	3M™ Escape Only Respirator Storage Bag	Replacement clear resealable storage bag for use with the 3M™ Escape Only Mouthpiece Respirator 5500 and 5600 Series.	20 ea/Case

3M™ Disposable Escape Only Mouthpiece Respirator 5600 Series

Air purifying escape only mouthpiece respirator offers a maintenance-free option with its simple design.



Part No.	Product Name	Description	Qty/Case
5602	3M™ Disposable Escape Only Mouthpiece Respirator, Acid Gas	NIOSH approved for protection against certain acid gases (Chlorine, Hydrogen Chloride, Sulfur Dioxide, Chlorine Dioxide, or Hydrogen Sulfide).	10 ea/Case
5604	3M™ Disposable Escape Only Mouthpiece Respirator, Ammonia/Methylamine	NIOSH approved for protection against ammonia and methylamine.	10 ea/Case



WARNING

This product helps protect against certain airborne contaminants. **Misuse may result in sickness or death.** For proper use, the

wearer must read and understand User Instructions provided as part of product packaging, see supervisor, or call 3M OH&ESD Technical Service, 1-800-243-4630 (U.S.A.). In Canada, call Technical Service at 1-800-267-4414. Time use limitations may apply.



Occupational Health and Environmental Safety Division
3M Center
Building 235-2NW-70
St. Paul, MN 55144-1000

For more information in the United States, contact:
Technical Assistance: 1-800-243-4630
Customer Service: 1-800-328-1667
Internet: www.3M.com/OccSafety

In Canada, contact:
Technical Assistance: 1-800-267-4414
3M Canada Customer Care: 1-800-364-3577
Internet: www.3M.ca/Safety
For other 3M Products:
Technical Assistance: 1-800-3M-HELPS

3M is a trademark of 3M Company, used under license in Canada. Please recycle. Printed in U.S.A. © 3M 2011. All rights reserved. dez_12017 70-0715-7481-1