

ALBION®

CASTERS AND WHEELS

NSF Stem Casters

- Double Row Swivel Raceways
- Heat Treated and Factory Lubricated Raceways
- Zinc Plated Finish



02RR04052S-S21
Friction Ring Stem



02XA05028S009
Friction Ring Stem



02IX04052S-S42
Threaded Stem



02IX04052S-S20
Threaded Stem

Applications: Hotel Equipment, Institutional Equipment, Food Service Racks and Cases, Stock Carts

| Wheel Dia. (In.) | Tread Width (In.) | Load Rating (lbs.) | Overall Height (In.) | Bearing Type | Stem Type | Stem Dimensions (In.) | Part Number |
|---------------------------|-------------------|--------------------|----------------------|----------------|------------------------|-----------------------|-----------------|
| Soft Rubber Wheel | | | | | | | |
| 3-1/2 | 1-1/4 | 150 | 4-3/8 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02RR03X52S-S21 |
| 3-1/2 | 1-1/4 | 150 | 4-3/8 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02RR03X52S-S20 |
| 3-1/2 | 1-1/4 | 150 | 4-3/8 | Delrin | Threaded | 1-1/2-13 x 1-1/2 | 02RR03X52S-S32 |
| 4 | 1-1/4 | 150 | 4-3/4 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02RR04052S-S21 |
| 4 | 1-1/4 | 150 | 4-3/4 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02RR04052S-S20 |
| 4 | 1-1/4 | 150 | 4-3/4 | Delrin | Friction Ring (2 ring) | 1 x 2-1/2 | 02RR04041S010 |
| 4 | 1-1/4 | 150 | 4-3/4 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02RR04052S-S42 |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02RR05052S-S21 |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02RR05052S-S20 |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Friction Ring | 13/16 x 1-3/4 | DCRR05052S-S22 |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Friction Ring (2 ring) | 1 x 2-1/2 | 02RR05041S017 |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Friction Ring | 0.845 x 2-3/16 | 02RR05041S014* |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Friction Ring | 0.845 x 2-3/16 | 02RR05041S015*+ |
| 5 | 1-1/4 | 200 | 5-11/16 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02RR05052S-S52 |
| TPR Rubber Wheel | | | | | | | |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IS03X52S-SX2 |
| 4 | 1-1/4 | 300 | 4-3/4 | Precision Ball | Friction Ring | 7/16 x 2-3/16 | 02XS04028S003 |
| 4 | 1-1/4 | 300 | 4-3/4 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IS04052S-S42 |
| 5 | 1-1/4 | 325 | 5-11/16 | Precision Ball | Friction Ring | 7/16 x 2-3/16 | 02XS05028S001 |
| 5 | 1-1/4 | 325 | 5-11/16 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IS05052S-S52 |
| Polyurethane Wheel | | | | | | | |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02IX03X52S-S21 |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02IX03X52S-S20 |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Threaded | 1/2-13 x 3/4 | 02IX03X52S-SX4 |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IX03X52S-SX2 |
| 4 | 1-1/4 | 350 | 4-3/4 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02IX04052S-S21 |
| 4 | 1-1/4 | 350 | 4-3/4 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02IX04052S-S20 |
| 4 | 1-1/4 | 350 | 4-3/4 | Delrin | Threaded | 1/2-13 x 3/4 | 02IX04052S-S44 |
| 4 | 1-1/4 | 350 | 4-3/4 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IX04052S-S42 |

(*) Includes rubber bumper, (+) Includes Strap brake



ALBION[®]

CASTERS AND WHEELS

NSF Stem Casters

| Wheel Dia. (In.) | Tread Width (In.) | Load Rating (lbs.) | Overall Height (In.) | Bearing Type | Stem Type | Stem Dimensions (In.) | Part Number |
|---------------------------|-------------------|--------------------|----------------------|--------------|------------------------|-----------------------|----------------|
| Polyurethane Wheel | | | | | | | |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02IX05052S-S21 |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02IX05052S-S20 |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Friction Ring | 13/16 x 1-3/4 | DCIX05052S-S22 |
| 5 | 1-1/4 | 250 | 5-11/16 | Ball | Friction Ring | 7/8 x 2-3/16 | 02XA05028S008 |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Friction Ring | 0.845 x 2-3/16 | 02XA05041S001 |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Friction Ring | 0.845 x 2-3/16 | 02XA05041S002+ |
| 5 | 1-1/4 | 250 | 5-11/16 | Ball | Friction Ring (2 ring) | 1 x 2-1/2 | 02XA05028S009 |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Threaded | 1/2-13 x 3/4 | 02IX05052S-S54 |
| 5 | 1-1/4 | 300 | 5-11/16 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IX05052S-S52 |
| Polyolefin Wheel | | | | | | | |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02IB03X52S-S21 |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02IB03X52S-S20 |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Threaded | 1/2-13 x 3/4 | 02IB03X52S-SX4 |
| 3-1/2 | 1-1/4 | 250 | 4-3/8 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IB03X52S-SX2 |
| 4 | 1-1/4 | 275 | 4-3/4 | Delrin | Friction Ring | 7/16 x 1-3/8 | 02IB04052S-S21 |
| 4 | 1-1/4 | 275 | 4-3/4 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02IB04052S-S20 |
| 4 | 1-1/4 | 275 | 4-3/4 | Delrin | Threaded | 1/2-13 x 3/4 | 02IB04052S-S44 |
| 4 | 1-1/4 | 275 | 4-3/4 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IB04052S-S42 |
| 5 | 1-1/4 | 350 | 5-11/16 | Delrin | Friction Ring | 7/16 x 1-29/32 | 02IB05052S-S20 |
| 5 | 1-1/4 | 350 | 5-11/16 | Delrin | Threaded | 1/2-13 x 3/4 | 02IB05052S-S54 |
| 5 | 1-1/4 | 350 | 5-11/16 | Delrin | Threaded | 1/2-13 x 1-1/2 | 02IB05052S-S52 |

(+) Includes Strap brake

