

ALBION[®]

CASTERS AND WHEELS

Total-Lock Scaffolding Casters

- Double Row Swivel Raceways
- Heat Treated and Factory Lubricated Raceways
- Zinc Finish

Applications: Work Platforms



02RR05041S016



02RR05052S019



02RR05041S018

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Stem Type	Stem Dimensions	Total-Lock Part Number
Soft Rubber Wheel (Delrin Bearing)						
5	1-1/4	240	6-3/16	Square	1-1/4" x 4" W/7/16" hole located 2-1/2" from bottom	02RR05041S016
5	1-1/4	240	6-3/16	Round	1-1/4" x 2-1/2" W/7/16" hole located 1" from bottom	02RR05052S019
5	1-1/4	240	6-3/16	Friction Ring	1.0475" x 2-3/4" W/7/16" hole located 1-1/4" from bottom	02RR05041S018

Ladder Casters

- Double Row Swivel Raceways
- Heat Treated and Factory Lubricated Raceways
- Zinc Finish

Applications: Ladders



02RN02052S001



02IB02041S001

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Stem Type	Stem Dimensions	Total-Lock Part Number
Soft Rubber Wheel (Delrin Bearing)						
2	13/16	75	2-1/2	Ladder Threaded Stem	5/16"-18 x 4-15/16"	02RN02052S001
3	13/16	100	3-1/2	Ladder Threaded Stem	5/16"-18 x 4-15/16"	02RN03052S001
Polyolefin Wheel (Plain Bearing)						
2	13/16	100	2-1/2	Ladder Threaded Stem	5/16"-18 x 4-15/16"	02IB02041S001
3	13/16	125	3-1/2	Ladder Threaded Stem	5/16"-18 x 4-15/16"	02IB03041S001

