

ALBION[®]

CASTERS AND WHEELS

Stem Casters Non-NSF

- Double Row Swivel Raceways
- Heat Treated and Factory Lubricated Raceways
- Zinc Plated Finish

Applications:

Fixtures, Carts, Institutional Equipment, Medical Equipment, Furniture



F1JW03027S-S60
Round Stem



F1RR05052S-S22
Friction Ring Stem



DCIS05052S-S30
Threaded Stem



F1IB04041S-S21
Friction Ring Stem

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Bearing Type	Stem Type	Stem Dimensions (In.)	Part Number
Soft Rubber Wheel							
2	13/16	75	2-1/2	Delrin	Friction Ring	7/16 x 1-3/8	F1RR02052S-S21
2	13/16	75	2-1/2	Delrin	Threaded	3/8-24 x 1-1/8	F1RR02052S-S12
2	13/16	75	2-1/2	Delrin	Threaded	1/2-13 x 1-1/2	F1RR02052S-S30
3	1	100	3-3/4	Delrin	Friction Ring	7/16 x 1-3/8	F1RR03052S-S21
3	1	100	3-3/4	Delrin	Friction Ring	7/16 x 1-29/32	F1RR03052S-S20
3	1	100	3-3/4	Delrin	Threaded	3/8-16 x 1-1/2	F1RR03052S-S10
3	1	100	3-3/4	Delrin	Threaded	7/16-14 x 1-1/2	F1RR03052S-S13
3	1	100	3-3/4	Delrin	Threaded	1/2-13 x 1-1/2	F1RR03052S-S30
3	1-1/4	150	3-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCRR03052S-S21
3	1-1/4	150	3-13/16	Delrin	Threaded	3/8-16 x 1	DCRR03052S-S11
3	1-1/4	150	3-13/16	Delrin	Threaded	7/16-14 x 1-1/2	DCRR03052S-S13
3	1-1/4	150	3-13/16	Delrin	Threaded	1/2-13 x 1	DCRR03052S-S31
3	1-1/4	150	3-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCRR03052S-S30
4	1	115	4-13/16	Delrin	Friction Ring	7/16 x 1-3/8	F1RR04052S-S21
4	1	115	4-13/16	Delrin	Friction Ring	7/16 x 1-29/32	F1RR04052S-S20
4	1	115	4-13/16	Delrin	Friction Ring	13/16 x 1-3/4	F1RR04052S-S22
4	1	115	4-13/16	Delrin	Threaded	3/8-16 x 1-1/2	F1RR04052S-S10
4	1	115	4-13/16	Delrin	Threaded	7/16-14 x 1-1/2	F1RR04052S-S13
4	1	115	4-13/16	Delrin	Threaded	1/2-13 x 1-1/2	F1RR04052S-S30
4	1-1/4	170	4-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCRR04052S-S21
4	1-1/4	170	4-13/16	Delrin	Threaded	3/8-16 x 1	DCRR04052S-S11
4	1-1/4	170	4-13/16	Delrin	Threaded	7/16-14 x 1-1/2	DCRR04052S-S13
4	1-1/4	170	4-13/16	Delrin	Threaded	1/2-13 x 1	DCRR04052S-S31
4	1-1/4	170	4-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCRR04052S-S30
5	1	125	5-13/16	Delrin	Friction Ring	7/16 x 1-3/8	F1RR05052S-S21
5	1	125	5-13/16	Delrin	Friction Ring	7/16 x 1-29/32	F1RR05052S-S20
5	1	125	5-13/16	Delrin	Friction Ring	13/16 x 1-3/4	F1RR05052S-S22
5	1-1/4	200	5-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCRR05052S-S21
5	1	125	5-13/16	Delrin	Threaded	3/8-16 x 1-1/2	F1RR05052S-S10
5	1	125	5-13/16	Delrin	Threaded	7/16-14 x 1-1/2	F1RR05052S-S13
5	1	125	5-13/16	Delrin	Threaded	1/2-13 x 1-1/2	F1RR05052S-S30
5	1-1/4	200	5-13/16	Delrin	Threaded	3/8-16 x 1	DCRR05052S-S11
5	1-1/4	200	5-13/16	Delrin	Threaded	7/16-14 x 1-1/2	DCRR05052S-S13
5	1-1/4"	200	5-13/16	Delrin	Threaded	1/2-13 x 1	DCRR05052S-S31
5	1-1/4	200	5-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCRR05052S-S30



ALBION[®]

CASTERS AND WHEELS

Stem Casters Non-NSF

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (Lbs.)	Overall Height (In.)	Bearing Type	Stem Type	Stem Dimensions (In.)	Part Number
TPR Rubber Wheel							
2	13/16	75	2-1/2	Plain	Friction Ring	7/16 x 1-3/8	F1IS02041S-S21
2	13/16	75	2-1/2	Plain	Friction Ring	7/16 x 1-29/32	F1IS02041S-S20
2	13/16	75	2-1/2	Plain	Threaded	3/8-16 x 1-1/2	F1IS02041S-S10
2	13/16	75	2-1/2	Plain	Threaded	1/2-13 x 1-1/2	F1IS02041S-S30
3	1-1/4	210	3-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCIS03052S-S21
3	1-1/4	210	3-13/16	Delrin	Threaded	3/8-16 x 1	DCIS03052S-S11
3	1-1/4	210	3-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCIS03052S-S30
4	1-1/4	300	4-13/16	Delrin	Threaded	3/8-16 x 1	DCIS04052S-S11
4	1-1/4	300	4-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCIS04052S-S30
5	1-1/4	325	5-13/16	Delrin	Threaded	3/8-16 x 1	DCIS05052S-S11
5	1-1/4	325	5-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCIS05052S-S30
Clear Polyurethane Wheel							
3	13/16	135	3-3/4	Precision Ball	Round	7/16 x 1-29/32	F1JW03027S-S60
3	13/16	135	3-3/4	Precision Ball	Friction Ring	7/16 x 1-3/8	F1JW03027S-S21
3	13/16	135	3-3/4	Precision Ball	Friction Ring	7/16 x 1-29/32	F1JW03027S-S20
3	13/16	135	3-3/4	Precision Ball	Threaded	3/8-16 x 1	F1JW03027S-S11
3	13/16	135	3-3/4	Precision Ball	Threaded	3/8-16 x 1-1/2	F1JW03027S-S10
3	13/16	135	3-3/4	Precision Ball	Threaded	1/2-13 x 1-1/2	F1JW03027S-S30
Gray Polyurethane Wheel							
3	1	125	3-3/4	Plain	Friction Ring	7/16 x 1-3/8	F1IX03041S-S21
3	1	125	3-3/4	Plain	Friction Ring	7/16 x 1-29/32	F1IX03041S-S20
3	1-1/4	210	3-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCIX03052S-S21
3	1	125	3-3/4	Plain	Threaded	3/8-16 x 1-1/2	F1IX03041S-S10
3	1	125	3-3/4	Plain	Threaded	1/2-13 x 1-1/2	F1IX03041S-S30
3	1-1/4	210	3-13/16	Delrin	Threaded	3/8-16 x 1	DCIX03052S-S11
3	1-1/4	210	3-13/16	Delrin	Threaded	7/16-14 x 1-1/2	DCIX03052S-S13
3	1-1/4	210	3-13/16	Delrin	Threaded	1/2-13 x 3/4	DCIX03052S-S32
3	1-1/4	210	3-13/16	Delrin	Threaded	1/2-13 x 1	DCIX03052S-S31
3	1-1/4	210	3-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCIX03052S-S30
4	1	140	4-13/16	Plain	Friction Ring	7/16 x 1-3/8	F1IX04041S-S21
4	1	140	4-13/16	Plain	Friction Ring	7/16 x 1-29/32	F1IX04041S-S20
4	1-1/4	275	4-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCIX04052S-S21
4	1	140	4-13/16	Plain	Threaded	3/8-16 x 1-1/2	F1IX04041S-S10
4	1	140	4-13/16	Plain	Threaded	1/2-13 x 1-1/2	F1IX04041S-S30
4	1-1/4	275	4-13/16	Delrin	Threaded	3/8-16 x 1	DCIX04052S-S11
4	1-1/4	275	4-13/16	Delrin	Threaded	7/16-14 x 1-1/2	DCIX04052S-S13
4	1-1/4	275	4-13/16	Delrin	Threaded	1/2-13 x 3/4	DCIX04052S-S32
4	1-1/4	275	4-13/16	Delrin	Threaded	1/2-13 x 1	DCIX04052S-S31
4	1-1/4	275	4-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCIX04052S-S30
5	1	145	5-13/16	Plain	Friction Ring	7/16 x 1-29/32	F1IX05041S-S20
5	1-1/4	300	5-13/16	Delrin	Friction Ring	7/16 x 1-3/8	DCIX05052S-S21
5	1	145	5-13/16	Plain	Threaded	3/8-16 x 1-1/2	F1IX05041S-S10
5	1	145	5-13/16	Plain	Threaded	1/2-13 x 1-1/2	F1IX05041S-S30
5	1-1/4	300	5-13/16	Delrin	Threaded	3/8-16 x 1	DCIX05052S-S11



ALBION[®]

CASTERS AND WHEELS

Stem Casters Non-NSF

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (Lbs.)	Overall Height (In.)	Bearing Type	Stem Type	Stem Dimensions (In.)	Part Number
Gray Polyurethane Wheel							
5	1-1/4	300	5-13/16	Delrin	Threaded	7/16-14 x 1-1/2	DCIX05052S-S13
5	1-1/4	300	5-13/16	Delrin	Threaded	1/2-13 x 3/4	DCIX05052S-S32
5	1-1/4	300	5-13/16	Delrin	Threaded	1/2-13 x 1	DCIX05052S-S31
5	1-1/4	300	5-13/16	Delrin	Threaded	1/2-13 x 1-1/2	DCIX05052S-S30
Polyolefin Wheel							
2	13/16	100	2-1/2	Plain	Friction Ring	7/16 x 1-3/8	F11B02041S-S21
2	13/16	100	2-1/2	Plain	Threaded	3/8-24 x 1-1/8	F11B02041S-S12
2	13/16	100	2-1/2	Plain	Threaded	1/2-13 x 1-1/2	F11B02041S-S30
3	1	125	3-13/16	Plain	Friction Ring	7/16 x 1-3/8	F11B03041S-S21
3	1	125	3-13/16	Plain	Friction Ring	7/16 x 1-29/32	F11B03041S-S20
3	1-1/4	210	3-13/16	Plain	Friction Ring	7/16 x 1-3/8	DCIB03041S-S21
3	1	125	3-13/16	Plain	Threaded	3/8-16 x 1-1/2	F11B03041S-S10
3	1	125	3-13/16	Plain	Threaded	7/16-14 x 1-1/2	F11B03041S-S13
3	1	125	3-13/16	Plain	Threaded	1/2-13 x 1-1/2	F11B03041S-S30
3	1-1/4	210	3-13/16	Plain	Threaded	3/8-16 x 1	DCIB03041S-S11
3	1-1/4	210	3-13/16	Plain	Threaded	7/16-14 x 1-1/2	DCIB03041S-S13
3	1-1/4	210	3-13/16	Plain	Threaded	1/2-13 x 3/4	DCIB03041S-S32
3	1-1/4	210	3-13/16	Plain	Threaded	1/2-13 x 1	DCIB03041S-S31
3	1-1/4	210	3-13/16	Plain	Threaded	1/2-13 x 1-1/2	DCIB03041S-S30
4	1	150	4-13/16	Plain	Friction Ring	7/16 x 1-3/8	F11B04041S-S21
4	1	150	4-13/16	Plain	Friction Ring	7/16 x 1-29/32	F11B04041S-S20
4	1-1/4	275	4-13/16	Plain	Friction Ring	7/16 x 1-3/8	DCIB04041S-S21
4	1	150	4-13/16	Plain	Threaded	3/8-16 x 1-1/2	F11B04041S-S10
4	1	150	4-13/16	Plain	Threaded	7/16-14 x 1-1/2	F11B04041S-S13
4	1	150	4-13/16	Plain	Threaded	1/2-13 x 1-1/2	F11B04041S-S30
4	1-1/4	275	4-13/16	Plain	Threaded	3/8-16 x 1	DCIB04041S-S11
4	1-1/4	275	4-13/16	Plain	Threaded	7/16-14 x 1-1/2	DCIB04041S-S13
4	1-1/4	275	4-13/16	Plain	Threaded	1/2-13 x 3/4	DCIB04041S-S32
4	1-1/4	275	4-13/16	Plain	Threaded	1/2-13 x 1	DCIB04041S-S31
4	1-1/4	275	4-13/16	Plain	Threaded	1/2-13 x 1-1/2	DCIB04041S-S30
5	1	150	5-13/16	Plain	Friction Ring	7/16 x 1-3/8	F11B05041S-S21
5	1	150	5-13/16	Plain	Friction Ring	7/16 x 1-29/32	F11B05041S-S20
5	1-1/4	300	5-13/16	Plain	Friction Ring	7/16 x 1-3/8	DCIB05041S-S21
5	1	150	5-13/16	Plain	Threaded	3/8-16 x 1-1/2	F11B05041S-S10
5	1	150	5-13/16	Plain	Threaded	7/16-14 x 1-1/2	F11B05041S-S13
5	1	150	5-13/16	Plain	Threaded	1/2-13 x 1-1/2	F11B05041S-S30
5	1-1/4	300	5-13/16	Plain	Threaded	3/8-16 x 1	DCIB05041S-S11
5	1-1/4	300	5-13/16	Plain	Threaded	7/16-14 x 1-1/2	DCIB05041S-S13
5	1-1/4	300	5-13/16	Plain	Threaded	1/2-13 x 3/4	DCIB05041S-S32
5	1-1/4	300	5-13/16	Plain	Threaded	1/2-13 x 1	DCIB05041S-S31
5	1-1/4	300	5-13/16	Plain	Threaded	1/2-13 x 1-1/2	DCIB05041S-S30

