

ALBION®

CASTERS AND WHEELS

Decorative Metal Ball Casters

- Self-Lubricating Acetyl Resin Bearing
- No Exposed Axle
- Chrome Finish

Applications: Furniture, Store Fixtures, Medical Equipment, Office Equipment



BCFS02041S001

BCFS02041S003

BCFS02041S005

BCRN03541S002

Wheel Dia. (In.)	Wheel Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Tread Type	Mounting Type	Mounting Dimensions	Swivel Part Number
------------------	-------------------	--------------------	----------------------	------------	---------------	---------------------	--------------------

Decorative Metal Ball Casters

2	2	80	2-3/16	Metal	Grip Neck Stem	5/16" x 1-1/2"	BCFS02041S001
2	2	80	2-3/16	Metal	Friction Ring Stem	3/8" x 1"	BCFS02041S003
2	2	80	2-3/16	Metal	Friction Ring Stem	7/16" x 1-3/8"	BCFS02041S004
2	2	80	2-3/16	Metal	Threaded Stem	5/16-18 x 1"	BCFS02041S005
2	2	80	2-1/2	Metal	Plate	1" x 1"	BCFS02041S002
2-1/2	2-1/2	100	2-11/16	Metal	Grip Neck Stem	5/16" x 1-1/2"	BCFS02441S001
2-1/2	2-1/2	100	2-11/16	Metal	Friction Ring Stem	3/8" x 1"	BCFS02441S003
2-1/2	2-1/2	100	2-11/16	Metal	Friction Ring Stem	7/16" x 1-3/8"	BCFS02441S004
2-1/2	2-1/2	100	2-11/16	Metal	Threaded Stem	5/16-18 x 1"	BCFS02441S005
2-1/2	2-1/2	100	3	Metal	Plate	1" x 1"	BCFS02441S002
3	3	100	2-7/8	Rubber	Grip Neck Stem	5/16" x 1-1/2"	BCRN03541S001
3	3	100	2-7/8	Rubber	Friction Ring Stem	3/8" x 1"	BCRN03541S003
3	3	100	2-7/8	Rubber	Friction Ring Stem	7/16" x 1-3/8"	BCRN03541S004
3	3	100	2-7/8	Rubber	Threaded Stem	5/16-18 x 1"	BCRN03541S005
3	3	100	3-3/16	Rubber	Plate	1" x 1"	BCRN03541S002

