

New Portable Patio Heaters

Our outdoor heaters are **designed to extend the use of your patio, deck or dining area.**
 The Crown Verity heater uses a standard 20 or 30 lb. propane cylinder (not included).



Stainless Steel
CV2650-SS

Silver Veined
CV2650-SV

Antique Bronze
CV2650-AB

cv-2650



Height (INCHES) 90.0	Base Diameter (INCHES) 18.25	BTUH (HOURLY) 45,000
Reflector Diameter (INCHES) 32.0	Net Weight Lbs. (NOT INCLUDING CYLINDER) 75.0	

- Completely self contained and portable
- Provides clean circle of warmth
- Piezo electric ignition system / fail safe pilot system
- Easy on / off tank access
- Weather resistant construction
- Adjustable heat output
- Easy to move wheel kit included
- CSA approved
- Available in several great finishes
- High output & fuel efficient conical burner
- Anti-tilt wheelbase with safety cut off switch

CROWN VERITY INC.



37 Adams Boulevard, Brantford, Ontario, Canada N3S 7V8
 tel 519.751.1800 fax 519.751.1802 e-mail info@crownverity.com web www.crownverity.com

Infrared Outdoor Patio Heaters

Models:

CV2650-SS Stainless Steel

CV2650-AB Antique Bronze

CV2650-SV Silver Veined

Specifications and Safety Features

Height:

90 inches

Reflector:

32 inches diameter, 16 gauge heavy duty reflector

Burner Materials:

All stainless steel construction

Emitter Grid Materials:

Heavy duty series 304 stainless steel, conical double wall construction

Fasteners:

Series 304 stainless steel

Major Components:

CV2650-SS 304 stainless steel (heater head assembly, post, base and decorative cover)
All other painted models (powder coated post, base and decorative cover)

BTU Input / Hour:

45,000 BTU/hour

Reflector Clearances:

18" from top - 24" to the sides

Base Diameter:

18.25 inches

Net Weight:

75 pounds (not including cylinder)

Circle Of Heat:

Varies 12 feet - 20 feet (3.6 - 6.1 meters) (will vary based on wind chill factor, prevailing winds, location of heater, wind protection)

Burn Time:

+10 hours on hi setting
(12 - 15 hours on low & medium)

Gas Pressure:

11.0 inches water column
(hose and regulator included)

Maximum supply inlet pressure:

100 psi

Gas Supply:

The unit is designed for propane fuel only - 20 or 30 lb. cylinders

Safety Systems:

100% safety shut-off +
Anti-tilt wheelbase with safety cut off switch

Product Approval:

USA and Canada approvals through CSA infrared patio heater standard

Commercial Warranty:

120 days limited parts only

CROWN VERITY INC.



37 Adams Boulevard, Brantford, Ontario, Canada N3S 7V8
tel 519.751.1800 fax 519.751.1802 e-mail info@crowneverity.com web www.crowneverity.com