



MODEL: HAULER 1200
TYPE: GASOLINE POWERED TRUCK
MODEL YEAR: 2014
Part No.: 618843



PRODUCT SPECIFICATION

CONFIGURATION HIGHLIGHTS

- Engine:** 13.5 hp (10.1 kW) Exceeds SAE J1940 Standard, 4 cycle, 24.5 ci (401 cc) single cylinder, air-cooled by Kawasaki
- Valve Train:** Overhead valve
- Fuel System:** Fixed float bowl with remote pulse fuel pump
- Lubrication:** Pressurized oil system, spin-on oil filter
- Ignition:** Electronic spark/magneto
- Balancer:** Internal counter rotating balance shaft
- Air Cleaner:** Replaceable dry cartridge
- Electrical:** Starter/Generator, solid-state regulator, 12 Volt maintenance free battery (425 CCA, 60 minute reserve)
- Drive Train:** Automatic, continuously variable transmission (CVT)
- Brakes:** Dual rear wheel mechanical self-adjusting drum brakes. Automatic single point park brake release with self-compensating system
- Transaxle:** Differential with helical gears, ground speed governor, forward/reverse
- Cargo Bed:** Roto-molded cross-linked polyethylene. Lifts for access to powertrain. Removable hinged multi-position tailgate requires no latch mechanism

PRODUCT OVERVIEW

Dimensions

Overall Length	113 in (287 cm)
Overall Width	49.5 in (128 cm)
Overall Height (No Canopy)	46.5 in (118 cm) (Top of steering wheel)
Overall Height (With Canopy)	70.0 in (178 cm)
Wheel Base	77.0 in (196 cm)
Front Wheel Track	37.0 in (94 cm)
Rear Wheel Track	38.0 in (97 cm)
Gnd Clearance @ Differential	4.3 in (11 cm)
Cargo Box Width (inside)	44.0 in (112 cm)
Cargo Box Length (inside)	36.0 in (91 cm)
Cargo Box Depth (inside)	10.5 in (27 cm)
Cargo Box Capacity	9.6 cu ft (0.27 m3)
Cargo Box material	Roto-molded polyethylene

Vehicle Power

Power Source	4 Cycle 24.5 cu in (401 cc)
Valve Train	Single Cylinder OHV
Horsepower (kW)	13.5 hp (10.1 kW) Exceeds SAE J1940 Std.
Electrical System	Starter/Generator. Solid State Regulator
Batteries (Qty, Type)	One, 12 Volt Maintenance Free
Key or Pedal Start	Pedal
Air Cleaner	Replaceable Dry Cartridge
Lubrication	Pressurized Oil System
Oil Filter	Spin-On
Cooling System	Air Cooled
Max Fuel Volume	6.0 Gallon (22.7 L) tank
Drive Train	Continuously variable transmission (CVT)
Transaxle	Differential with helical gears
Gear Selection	Forward - Reverse
Rear Axle Ratio	11.42:1 (Forward) 15.78:1 (Reverse)

Performance

Seating Capacity	2 Persons
Dry Weight	938 lb (425 kg)
Curb Weight	978 lb (443 kg)
Bed Load Capacity	800 lb (364 kg)
Vehicle Load Capacity	1200 lb (545 kg)
Outside Clearance Circle	22.0 ft (6.7 m)
Intersecting Aisle Clearance	N/A
Speed (Level Ground)	Fwd - 16.5 mph ± 0.5 mph (25.7 kph ± 0.8 kph) Rev - 11.6 mph ± 0.5 mph (18.6 kph ± 0.8 kph)
Towing Capacity	720 lb (360 kg) max load

Steering & Suspension

Steering	Self-compensating rack and pinion
Front Suspension	Leaf springs with hydraulic shock absorbers
Rear Suspension	Leaf springs with hydraulic shock absorbers
Service Brake	Rear wheel mechanical self-adjusting drum
Parking Brake	Self-compensating, single point engagement
Front Tires	Links 18 x 8.50 - 8 (4 Ply Rated)
Rear Tires	Turf Saver 20 x 10.0 - 8

Body & Chassis

Frame	Welded steel with DuraShield™ powder coat
Front Body & Finish	Injection Molded TPO
Rear Body & Finish	Steel. Base coat/clear coat
Standard Color	Forest Green

Some items shown may be optional equipment



OPTIONS & FIELD INSTALLED ACCESSORIES (Installation not included)*

TIRES & WHEELS:

Front:			
Links 18 x 8.50 - 8 (4 Ply Rated)	X		
USA Trail 18 x 8.50 - 8 (Load Range C)		X	
Turf Saver 18 x 8.50 - 8 (Load Range B)		X	
Rear:			
Turf Saver 20 x 10 - 10	X		
Links 18 x 8.50 - 8 (4 Ply Rated)		X	
USA Trail 18 x 8.50 - 8 (Load Range C)		X	
Turf Saver 18 x 8.50 - 8 (Load Range B)		X	
Wheel Covers:			
Spoke, Gold		X	
Spoke, Silver		X	

COLORS:

Body Color - Forest Green	X		
Body Color - Ivory		X	
Body Color - Bright White		X	
Body Color - Yellow		X	
Body Color - Orange		X	
Custom Body Color		X	

SEATS:

Seat Color - Gray	X		
Seat Color - Oyster		X	
Seat Color - Tan		X	
Seat Color - White		X	

HAULING & TOWING:

Poly Bed w/Manual Dump	X		
Poly Bed w/Electric Dump		X	
Alum Bed w/Manual Dump		X	
Alum Bed w/Electric Dump		X	
2 in (5 cm) Receiver (Rear)		X	
1 7/8 in (48 mm) Ball Hitch (Rcvr Req'd)		X	
Angle Hitch (Rcvr Req'd)		X	
Clevis Hitch (Rcvr Req'd)		X	
Angle Hitch, Drop (Rcvr Req'd)		X	
1 7/8 in (48 mm) Ball Hitch, Drop (Rcvr Req'd)		X	
Clevis Hitch, Drop (Rcvr Req'd)		X	

OTHER PERFORMANCE:

Front Fascia & Brush Guard (Black)	X		
Ash Tray		X	
Front Hydraulic Disc Brakes		X	
Glove Box Door (Locking) Driver Side		X	
Glove Box Door (Locking) Passenger Side		X	
International Shipping		X	

Electrical:

Headlights		X	
LED Headlights			X
Headlights & Taillights			X
Unique Individual Key Switch			X
Brake Lights			X
Turn Signals with 4-Way Flashers			X
Horn		X	
State of Charge Meter		X	
HD Battery			X
Hour Meter			X
12V Power Outlet			X

TRANSAXLE:

Limited Slip Differential			X
High Altitude			X

WEATHER PROTECTION:

Sun Canopy (Top) Black			X
Windshield Fold Down			X
Windshield Flat			X
Weather Enclosure (Top & W'shld Req'd) various colors			X
Canopy Handle			X

VEHICLE CAB:

Steel Cab (Tan):			X
Steel Cab (White):			X
Steel Cab (Custom Color):			X
Doors (Steel) Tan (Cab Req'd)			X
Doors (Steel) White (Cab Req'd)			X
Doors (Steel) Custom Color (Cab Req'd)			X
Doors (Vinyl) Tan (Cab Req'd)			X
Beacon, Amber (Cab, Fuse Panel w/Switches Req'd)			X
Defroster/Fan (Cab, Fuse Panel w/Switches Req'd)			X
Dome Light (Cab, Fuse Panel w/Switches Req'd)			X
Rear View Mirror (Cab Req'd)			X
Strobe Light (Cab, Fuse Panel w/Switches Req'd)			X
Windshield Wiper (Cab, Fuse Panel w/Switches Req'd)			X
Work Light (Cab, Fuse Panel w/Switches Req'd)			X
Fuse Panel w/Switches			X