

## Side Mount Designer Combination LED Unit

### FEATURES

- Side mounted combo unit for commercial applications
- Optional LED based MR-16 lamps available for increased coverage and remote capacity
- High-impact, 5VA flame rated, UV stabilized, white thermoplastic housing
- Universal end/ceiling/wall mount and included canopy
- Fully adjustable, high output, MR16 halogen lamp heads
- Energy saving, long-life LED lamps exceed brightness and uniformity requirements
- Snap-in chevron arrows; 6" letters with 3/4" stroke
- Remote capacity with or without lamp heads
- Maintenance-free lead-acid battery with fully automatic charger
- Temperature range: 20°C to 30°C (68°F to 86°F)
- UL 924 Listed



### ORDERING INFORMATION

<b>HCX</b>				-	
<b>MODEL</b>	<b>FACES</b>	<b>LETTER COLOR</b>	<b>HOUSING FINISH</b>		<b>OPTIONS</b>
HCX	U Universal Single/ Double Face	R Red G Green	W White B Black		Blank 5W Halogen lamps O3L 3W LED lamps RC12 12W Remote Capacity (includes lighting heads) <sup>1,2</sup> O-RC12 23W Remote Capacity (no lighting heads). Available in white only. <sup>1,2</sup>

<sup>1</sup> RC12 option can be specified with the -O3L option.  
Example: HCXURW-O3LRC12

<sup>2</sup> No lamp-head option only available with remote capacity model

### ACCESSORIES

MODEL	DESCRIPTION
WGTW	Wire guard (wall mount)
WGTC	Wire guard (ceiling mount)

### ELECTRONICS

- Transformer isolation, surge, transient, and low voltage disconnect protection
- Pre-stripped pigtail leads
- 90 minute emergency operation
- Reverse polarity, short circuit and AC lockout protection
- 120/277VAC 60Hz operation, test switch and LED AC-On indicator light

### MATCHING REMOTE HEADS

#### MATCHING 5W INDOOR REMOTE HEADS

CPRSW0605	Single, White
CPRDW0605	Double, White
CPRSB0605	Single, Black
CPRDB0605	Double, Black

#### MATCHING 5W OUTDOOR REMOTE HEADS

OCRSW0605	Single, White
OCRDW0605	Double, White
OCRSB0605	Single, Black
OCRDB0605	Double, Black
OCRSZ0605	Single, Dark Bronze
OCRDZ0605	Double, Dark Bronze

#### MATCHING 3W LED REMOTE HEADS

OCRSW0603L	Single, White
OCRDW0603L	Double, White
OCRSB0603L	Single, Black
OCRDB0603L	Double, Black
OCRSW1203L	Single, White
OCRDW1203L	Double, White
OCRSB1203L	Single, Black
OCRDB1203L	Double, Black

### POWER CONSUMPTION

	120VAC	277VAC
Red, Green Models	4.5W	4.5W

Power factor, average: .80 (lagging)  
Wattage figures include LED lamps, transformers and electronics power requirements.

