

GX SERIES ENGINES

GX SERIES		GX270UT2
	Variation	QXC9
Crankshaft	Q-Type 3.48" x 1.0" Dia	•
	R-Type 2:1 w/Wet Clutch; 2.09" x 22mm	
Throttle Control	Manual	•
	Remote (Wire)	
	Remote (Rod)	•
Choke Control	Manual	•
Electric Start	12V dc Motor/Control Box	
Charging System	3 Amp	
	18 Amp	
Oil	Alert (Engine Shutdown)	•
Air Cleaner	Dual Element	
	Cyclone	•
Muffler	Standard	
	Silent	•
	Round/Water Pump Style	
	Spark Arrester	
	Deflector	

Q-TYPE

