

G5 Latex[†] 12" Ambi Gloves

Product Codes: 56809, 56810, 56811, 56812

Technical Data Sheet



Product Information

Code	Affiliate #	Size	Palm Width*(mm)	Length* (mm)	Quantity
56809	HC2211	S	85	305	100 gloves/bag; 10 bags/case
56810	HC3311	M	96	305	100 gloves/bag; 10 bags/case
56811	HC4411	L	112	305	100 gloves/bag; 10 bags/case
56812	HC5511	XL	118	305	100 gloves/bag; 10 bags/case

*As measured by ASTM D 3578; 2.5 AQL¹

Property	Description
General Description	Natural rubber, powder free, cleanroom gloves, straight finger, ambidextrous former with non-slip/textured finish at palm and fingers, beaded cuff, 10" nominal length. KIMTECH PURE G5 Latex gloves are certified Category III PPE classified by EC Council Directive 89/686/EEC.

Physical Property	Unit	Upper Limit	Test Method (1.5 AQL)
Watertightness	NA	Pass	ASTM D 5151
Particulate Level ≥0.5 microns	#/cm ²	3000	IEST-RP-CC005

Thickness	Nominal	Nominal	Test Method (2.5 AQL)
Middle Finger	8.27 mil	0.21 mm	ASTM D 6319
Palm	7.09 mil	0.18 mm	ASTM D 6319
Cuff	4.72 mil	0.12 mm	ASTM D 6319

Property	Tensile Strength	Ultimate Elongation	Median Force at Break
Before Aging	14.0 Mpa	500%	5.2 Newtons
After Aging	14.0 Mpa	400%	3.5 Newtons
Testing Method	ASTM D 412 ASTM D 6319 ASTM D 573	ASTM D 412 ASTM D 6319 ASTM D 573	EN 455-2

¹ AQL levels defined according to ISO 2859-1 (current edition) Sampling Procedures for Inspection by Attributes.

[†] This product contains natural rubber latex, which may cause allergic reactions. Safe use of this glove by or on latex sensitive individuals has not been established. This product should not be worn, or exposed to, individuals allergic to natural rubber latex.

Workmanship Requirement:

Gloves shall be made in accordance with reasonable industry practice with respect to defects, dirt and contamination. Gloves should be packaged as specified having described size and color in the appropriate quantity as listed. Shipping Case and inner packaging shall be labeled with product name, size, lot/batch and catalog number.

For additional information: 1-800-255-6401 or kimtech@kcc.com

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. **THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

®/™Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © 2013 KCWW.

Rev: Feb 2013