

# Universal Centrifuge

With the choice of either an 8 place fixed-angle rotor or a 6 place swing-out rotor, the Universal Centrifuge from LW Scientific is the perfect solution for both laboratories and doctors' offices. This newest member of our USA centrifuge initiative features a ZERO-RPM locking lid for safety and digital programming of time and speed ranging from 800-3400rpm. Achieve up to 1550g with the fixed angle rotor and 1809g with the swing-out rotor resulting in clean, easy to read lines of separation. The LW Scientific Universal centrifuge has a 110-220v auto-switching power adapter.

## ADVANTAGES

Accurate speeds for specific g-force  
Ideal for blood, urine, and other fluids

## DESIGN FEATURES

Rubber feet to prevent slipping  
Easy removal of rotors for accessibility  
*Choice of rotor:*  
-8-place angled  
-6-place swing-out  
Zero-rpm locking lid  
Service Indicator Light  
Stores last four programmed speeds

## SPECIFICATIONS

800-3400 rpm  
Maximum RCF:  
1550g with fixed-angle  
1809g with swing-out  
12 volt maintenance-free brushless motor  
Programmable Digital Time and Speed  
Fixed angle rotor: 8-place 3-15ml tubes  
Swing-out rotor: 6-place 3-15ml tubes  
110/220v auto-switching power adapter  
53 dBA +/- 3 dBA @ 18"-24"

## INCLUDES

Power adapter (CE, UL, cUL approved)  
*8-place fixed-angle rotor*  
-8 small tube shields  
(accommodates min. tube size of 10.25x65mm)  
-8 large tube shields  
(accommodates max. tube size of 17x130mm)  
**or**  
*6-place metal rotor*  
-6 small tube shields  
(accommodates min. tube size of 10.25x65mm)  
-6 large tube shields  
(accommodates max. tube size of 17x130mm)

## CONTROLS

Touch Pad time and speed controls  
800-3400 rpm programmable

## WEIGHT AND DIMS

Height: 10.65" (270 mm)  
Length: 14.5" (368 mm)  
Width: 14.5" (368 mm)  
Weight: 11.6 lb (5.26 kg)



Designed, Engineered & Assembled  
Proudly in America

## Universal

Model #	Description
UNC-08AD-15T3	8-place angled rotor, digital
UNC-06SD-15T3	6-place swing-out rotor, digital

- Programmable Digital Time and Speed
- Variable Speed, 800-3400 rpm



P 770.270.1394  
F 770.270.2389

865 Marathon Parkway  
Lawrenceville GA 30046

LWScientific.com