

A00110 Oven & Grill Cleaner

Cleaning



Features

- Aggressive Caustic Formula
- Thickened Formula Clings to Vertical Surfaces
- Very Aggressive, Heavy Duty Formula
- 360° Valve Allows Can to Spray Upside Down
- Easily Removes Baked on Deposits

Description

Formulated for hard-to-clean institutional ovens and cooking utensils. Works extremely well on outdoor barbecue grills, both gas and charcoal. Home ovens and pots and pans are cleaned easily, with far less effort than with conventional cleaners. Shines stainless steel to look like new. Do not allow cleaner to remain on asphalt tile. Do not use on aluminum.

TECHNICAL INFO:		
Physical Properties	Appearance	Foamy Spray, Thick
	Color	Off-White
	Odor/Fragrance	Lemon
	pH	13.0-14.0
	Spray Pattern	Oval
Environmental Profile	Glycol Ether Content	No
	Biodegradability	Yes (Surfactants)
	Chlorinated Solvents	No
	Green Status	None
	Recyclable Packaging	Yes
Regulatory Profile	% VOC By Weight	8.0
	VOC Restricted Regions	None
	Food Processing Suitability	A8
	EPA #	N/A
	Flammability per CPSC	NCAF
	NFPA Code 30B Storage Level	1



Packages Available:



Label Datecode: 08/92

Manufactured by:

amrep
PROFESSIONAL PRODUCTS GROUP inc.

990 Industrial Park Drive • Marietta, GA 30062
800-241-7766 • 770-422-2071 • Fax: 770-422-1737
www.amrep.com