

MORSE
THE M. K. MORSE COMPANY

811

PATENT
PENDING

BANDSAW BLADES

PORTABLE BANDS

▼ **INCREASED PRODUCTIVITY & COST SAVINGS**

- One Morse 811™ Saw Blade replaces the need for blades from 8/12 through 18 TPI (Teeth per inch)
- Band Saws cut Solids from 1/8" to 3" in diameter & Structural Shapes with 1/16" - 3/8" Wall thickness
- Less time changing blades and less inventory to stock

▼ **QUICK, CLEAN CUTS IN MORE MATERIALS**

- Mild Steel, Tool Steel, Stainless Steel, Brass, Plastic & Wood
- Cuts everything you do with ONE BLADE

▼ **TYPICAL USERS**

- Weld Shops, Tool Rooms, Maintenance Rooms, Job Shops, Machine Shops



CUT MORE WITH LESS

BANDSAW BLADES

Grainger #	Morse Model #	Length	Width & Thickness	TPI	PKG
20UJ40	4052800644-WWG	5ft 4-1/2in	1/2" x .035"	8/11	1
20UJ41	4052800930-WWG	7ft 9in	1/2" x .035"	8/11	1
20UJ42	9154800930-WWG	7ft 9in	3/4" X .035"	8/11	1
20UJ43	9154801140-WWG	9ft 6in	3/4" X .035"	8/11	1
20UJ44	9154801200-WWG	10ft	3/4" X .035"	8/11	1
20UJ45	9154801300-WWG	10ft10in	3/4" X .035"	8/11	1
20UJ46	9154801380-WWG	11ft 6in	3/4" X .035"	8/11	1
20UJ47	9154801740-WWG	14ft 6in	3/4" X .035"	8/11	1
20UJ48	9155800930-WWG	7ft 9in	1" X .035"	8/11	1
20UJ49	9155801060-WWG	8ft 10in	1" X .035"	8/11	1
20UJ50	9155801140-WWG	9ft 6in	1" X .035"	8/11	1
20UJ51	9155801200-WWG	10ft	1" X .035"	8/11	1
20UJ52	9155801300-WWG	10ft 10in	1" X .035"	8/11	1
20UJ53	9155801350-WWG	11ft 3in	1" X .035"	8/11	1
20UJ54	9155801380-WWG	11ft 6in	1" X .035"	8/11	1
20UJ55	9155801500-WWG	12ft 6in	1" X .035"	8/11	1
20UJ56	9155801710-WWG	14ft 3in	1" X .035"	8/11	1
20UJ57	9155801740-WWG	14ft 6in	1" X .035"	8/11	1
20UJ58	9161801800-WWG	15ft	1-1/4" X .042"	8/11	1

PORTABLE BANDS

Grainger #	Morse Model #	Length	Width & Thickness	TPI	PKG
20UJ59	002653-WWG	27-3/16	1/2" x .020"	8/11	3/PK
20UJ60	002660-WWG	28-13/16	1/2" x .020"	8/11	3/PK
20UJ61	002677-WWG	32-7/8	1/2" x .020"	8/11	3/PK
20UJ62	002684-WWG	35-3/8	1/2" x .020"	8/11	3/PK
20UJ65	002486-WWG	44-7/8	1/2" x .020"	8/11	3/PK
20UJ64	002462-WWG	44-7/8	1/2" x .020"	8/11	25/PK
20UJ63	002455-WWG	44-7/8	1/2" x .020"	8/11	100/PK

For more information contact your **Grainger Representative** or visit **Grainger.com**®

AVAILABLE THROUGH