

Office Pro® 12

MOVINCOOL®
THE #1 SPOT COOLING SOLUTION

The MovinCool Office Pro 12 portable air-conditioner is specifically designed for offices filled with heat generating electronics. Computers, networks, communications and office equipment will shut down when the temperature rises, crippling daily operations.

By bringing spot air-conditioning to just the area or room that needs it, the Office Pro saves money while protecting your company's investment in equipment and customers. Self-contained and portable, the Office Pro 12 requires no costly installation, simply roll it in, plug it in and turn it on.

- Provides 12,000 Btu/h of cool air, maximum spot cooling to just the room that needs it
- Programmable digital controller
- Operates on standard 115V power, can be used anywhere for as little as 15 cents per hour
- No costly installation necessary, roll it in, plug it in, turn it on
- Provides cooling down to 65°F, the ideal operating temperature for heat sensitive electronics



MOVINCOOL®

THE #1 SPOT COOLING SOLUTION

800.264.9573
www.movincool.com

DENSO SALES CALIFORNIA, Inc. 3900 Via Oro Ave. Long Beach, CA 90810



TECHNICAL SPECS		OFFICE PRO® 12
Electronic Features	Control	Programmable
Cooling Capacity	Rating Conditions: 95°F at 60% RH	12,000 Btu/h
Electrical Characteristics	Voltage Requirements Total Power Consumption Current Consumption Recommended Fuse Size NEMA Plug Configuration Min. – Max. Voltage	1 Phase, 115V 1.3 kW 11.9 amps 15 amps 5 - 15 105 - 125
Fans	Motor Output - high/low	0.14/0.08 kW
Evaporator	Fan Type Max. Air Flow - high/low Max. External Static Pressure	Centrifugal 410/380 CFM 0.31 IWG
Condenser	Fan Type Max. Air Flow - high/low Max. External Static Pressure	Centrifugal 820/715 CFM 0.16 IWG
Compressor	Type Output	Hermetic Rotary 0.9 kW
Refrigerant	Type	R-410A
Dimensions	W x D x H	21 x 27 x 44 in
Net Weight/Shipping Weight		151/182 lb
Power Cord	Gauge/Length	14 AWG (3-core)/10 ft
Condensate Tank Capacity		5 gal
Operating Conditions	Min. – Max. (@ 50% RH)	65° - 95°F
Max. Equivalent Duct Length	Per Cold Duct Hose Hot Duct Hose	30 ft 60 ft
Max. Sound Level	With Condenser - Duct high/low Without Condenser - Duct high/low	52/50 dB(A) 55/53 dB(A)

All specifications subject to change without notice.

© 2013 DENSO SALES CALIFORNIA, INC. MovinCool, SpotCool and Office Pro are registered trademarks of DENSO Corporation.
360-0213-0P12

