

# Office Pro® 18

MOVINCOOL®  
THE #1 SPOT COOLING SOLUTION

Delivering the highest cooling capacity possible from a standard 115V power source, the Office Pro 18 portable air conditioner helps companies cool their heat-sensitive office systems and protects against the loss of data. The Office Pro 18 features easy-to-use programmable controls allowing automatic operation after-hours or during weekends when heat can cause damage to expensive office equipment.

The Office Pro 18 makes air conditioning solutions a breeze through its self-contained, portable design. No costly installation is necessary so the Office Pro 18 can simply be wheeled in, plugged into a standard 115V power source and switched on, instantly providing up to 16,800 Btu/h.

- Delivers the highest cooling capacity possible from a standard 115V power source
- Operates automatically after-hours or weekends with easy-to-use programmable controls
- Totally self-contained, portable design
- Quick, easy and cost-effective installation



# MOVINCOOL®

THE #1 SPOT COOLING SOLUTION

800.264.9573  
www.movincool.com

DENSO SALES CALIFORNIA, Inc. 3900 Via Oro Ave. Long Beach, CA 90810



TECHNICAL SPECS		OFFICE PRO® 18
Electronic Features	Control	Programmable
Cooling Capacity	Rating Conditions: 95°F at 60% RH	16,800 Btu/h
Electrical Characteristics	Voltage Requirements Total Power Consumption Current Consumption Recommended Fuse Size NEMA Plug Configuration Min. – Max. Voltage	1 Phase, 115V 1.7 kW 15.6 amps 20 amps 5 - 20 105 - 125
Fans	Motor Output - high/low	0.24/0.17 kW
Evaporator	Fan Type Max. Air Flow - high/low Max. External Static Pressure	Centrifugal 540/500 CFM 0.31 IWG
Condenser	Fan Type Max. Air Flow - high/low Max. External Static Pressure	Centrifugal 770/710 CFM 0.23 IWG
Compressor	Type Output	Hermetic Rotary 1.16 kW
Refrigerant	Type	R-410A
Dimensions	W x D x H	21 x 27 x 44 in
Net Weight/Shipping Weight		170/201 lb
Power Cord	Gauge/Length	12 AWG (3-core)/10 ft
Condensate Tank Capacity		5 gal
Operating Conditions	Min. – Max. (@ 50% RH)	65° - 95°F
Max. Equivalent Duct Length	Per Cold Duct Hose Hot Duct Hose	25 ft 100 ft
Max. Sound Level	With Condenser - Duct high/low Without Condenser - Duct high/low	61/59 dB(A) 62/60 dB(A)

All specifications subject to change without notice.

© 2013 DENSO SALES CALIFORNIA, INC. MovinCool, SpotCool and Office Pro are registered trademarks of DENSO Corporation.  
360-0213-0P18

