





# PolyTac™ LED HP Tactical Light

FL1 STANDARD	POLYTAC LED HP
	<b>150</b> LUMENS
	<b>3h</b>
	<b>245m</b>
	<b>15,000cd</b>



**Case Material:** High impact super tough nylon polymer for exceptional durability and a sure grip. All openings o-ring sealed for weather resistance. Available in black, coyote or yellow.

**Dimensions:** Length: 5.65 in. (14.35 cm)      Major Diameter: 1.70 in. (4.32 cm)      Body Diameter: 1.00 in. (2.54 cm)

**Weight:** 4.4 oz (125 grams)\*

**Lens:** Unbreakable polycarbonate with scratch-resistant coating, o-ring sealed.

**Light Source:** C4 LED technology, impervious to shock with a 50,000 hour lifetime.

**On/Off:** Tailcap push button provides one handed momentary or constant "on" operation.

**Battery:** Two CR123A lithium batteries

**Features:**

- LED Solid State Power Regulation provides maximum light output throughout battery life
- IPX7 rated design; waterproof to 1 meter for 30 minutes.

**Approvals:** Most models meet applicable European Community Directives

**Warranty:** Limited lifetime warranty

\*With batteries (included in purchase).



Item	UPC	Part #
PolyTac LED HP with lithium batteries - Black	080926-88860-9	88860
PolyTac LED HP with lithium batteries - Yellow	080926-88863-0	88863
Rubber helmet strap	080926-99075-3	99075
Lithium batteries (2) Pack	080926-85175-7	85175
Lithium batteries (12) Pack	080926-85177-1	85177
Lithium batteries (400) Pack	080926-85179-5	85179
Lithium batteries (6) Pack	080926-85180-1	85180

