



JAN/SAN

APPLICATIONS & DILUTIONS

Also available in:



SIMPLE GREEN® INDUSTRIAL CLEANER & DEGREASER

- Non-toxic and biodegradable formula
- Non-abrasive and non-flammable
- Mild 9.0 +/- 0.5 pH
- Safer alternative to harsh chemical, solvents and detergents
- Available in original sassafras scent or lemon scent



1:3 - 1:5



1:3 - 1:5



1:3 - 1:5



1:10 - 1:15



1:20 - 1:25



1:30 - 1:35



1:30 - 1:35



1:30 - 1:35



1:40 - 1:50

DILUTION RATIO: The 1st number represents the amount of Simple Green product recommended. The 2nd number represents the amount of water. (Second ratio given is for Crystal Simple Green)



Nonfood Compounds
Program Listed A1, A2,
A4, A8, B1, C1 #145909



CRYSTAL SIMPLE GREEN® INDUSTRIAL CLEANER & DEGREASER

- Non-toxic and biodegradable formula
- No color and no added scent
- Non-abrasive and non-flammable
- Clean rinsing
- NSF A1, A2, A4, A8, B1 & C1 ratings



SIMPLE GREEN LIME SCALE REMOVER

- Non-abrasive and non-flammable
- Contains no bleach, ammonia or phosphorous
- Organic salt formula
- Fresh wintergreen scent

EPA REGISTERED
DISINFECTANTS

d PRO 3®



d PRO 5®

SIMPLE GREEN d PRO 3®

- One-step hospital-grade disinfectant, cleaner, deodorizer • Kills MRSA, HIV-1, Influenza A and more
- Fresh herbal-pine scent

SIMPLE GREEN d PRO 5®

- Blood borne pathogen disinfectant cleaner
- Kills MRSA, HIV-1, Influenza A, Hep B & C, and more • No added color or scent



SIMPLE GREEN® CARPET CLEANER

- Non-toxic and biodegradable formula
- Institutional formulation
- No color added
- Zero VOCs – fragrance free
- Brightens without bleach



PARTS WASHERS

- Corrosion resistant construction, longer lasting components
- Heating elements—heat preset to 110°F
- Ground fault interrupter



PROPORTIONERS

- 0800000113384: 4 pre-set dilutions-1 gpm
- 0800000113385: up to 5 products; 4@ 1 gpm; 1@ 4 gpm
- Ensure proper mixing for specific applications
- Save money by cutting material usage
- Minimize excessive packaging disposal



SIMPLE GREEN STAINLESS STEEL® ONE-STEP CLEANER & POLISH

- Non-aerosol spray cleans and polishes in a single step
- Non-toxic and non-flammable formula
- Resists dust, water and finger marks with no oily finish



JAN/SAN

APPLICATIONS & DILUTIONS CHART

PRODUCT DESCRIPTION

SIMPLE GREEN® INDUSTRIAL CLEANER & DEGREASER

- Non-toxic and biodegradable formula
- Non-abrasive and non-flammable
- Mild 9.0 +/- 0.5 pH
- Safer alternative to harsh chemical, solvents and detergents
- Available in sassafras scent or lemon scent

CRYSTAL SIMPLE GREEN® INDUSTRIAL CLEANER & DEGREASER

- Non-toxic and biodegradable formula
- No color and no added scent
- Non-abrasive and non-flammable
- Clean rinsing
- NSF A1, A2, A4, A8, B1 & C1 ratings

SIMPLE GREEN LIME SCALE REMOVER

- Non-abrasive and non-flammable
- Contains no bleach, ammonia or phosphorous
- Organic salt formula
- Fresh wintergreen scent

SIMPLE GREEN® d PRO 3

- One-step hospital-grade disinfectant, cleaner, deodorizer
- Kills MRSA, HIV-1, Influenza A and more
- Fresh herbal-pine scent

SIMPLE GREEN® d PRO 5

- One-step disinfectant virucide, fungicide, mildewstat, cleaner and sanitizer
- Blood-borne pathogen compliant disinfectant
- Kills MRSA, HIV-1, Influenza A, Hep B & C, and more
- No added color or scent

• SANITIZING DILUTION >>>

SIMPLE GREEN STAINLESS STEEL® ONE-STEP CLEANER & POLISH

- Non-toxic and biodegradable
- Non-petroleum, zero VOC's
- Non-abrasive and non-flammable
- Cleans and polishes, stainless steel, chrome, metal surfaces, and more

PROPORTIONERS

- Various configurations available for multiple products and dilutions
- Ensure proper mixing for specific applications
- Save money by cutting material usage
- Lockable wire racks also available

PARTS WASHERS

- Corrosion resistant construction, longer lasting components
- Heating elements—heat preset to 110°F
- Ground fault interrupter

PRODUCT DESCRIPTION	LOCATIONS												PRODUCT NUMBER	
	Office/Public Areas	Locker Rooms/Showers	Restrooms	Maintenance Areas	Warehouse/Distribution	Cafeterias/Break Areas	Medical Facilities	Carpet & Upholstery	Floors	Garbage Cans/Dumpsters	Windows/Glass	Laundry		Fleet Vehicles
SIMPLE GREEN® INDUSTRIAL CLEANER & DEGREASER <ul style="list-style-type: none"> • Non-toxic and biodegradable formula • Non-abrasive and non-flammable • Mild 9.0 +/- 0.5 pH • Safer alternative to harsh chemical, solvents and detergents • Available in sassafras scent or lemon scent 	1:30	1:10	1:10	1:20	1:20	1:10	1:20	1:40	1:30	1:10	1:140	1/4 Cup per full load	1:30	24 oz Trigger 2710001213012 1 gal Bottle 2710200613005 5 gal Pail 2700000113006 15 gal Pail 2700000113016 55 gal Drum 2700000113008 275 gal Tote 2700000113275
CRYSTAL SIMPLE GREEN® INDUSTRIAL CLEANER & DEGREASER <ul style="list-style-type: none"> • Non-toxic and biodegradable formula • No color and no added scent • Non-abrasive and non-flammable • Clean rinsing • NSF A1, A2, A4, A8, B1 & C1 ratings 	1:40	1:20	1:20	1:20	1:30	1:20	1:30	1:50	1:40	1:20	1:150	1/4 Cup per full load	1:50	24 oz Trigger 0610001219024 1 gal Bottle 0610000619128 5 gal Pail 0600000119005 55 gal Drum 0600000119055 275 gal Tote 0600000119275
SIMPLE GREEN LIME SCALE REMOVER <ul style="list-style-type: none"> • Non-abrasive and non-flammable • Contains no bleach, ammonia or phosphorous • Organic salt formula • Fresh wintergreen scent 	RTU to 1:4	RTU to 1:4	RTU to 1:4	RTU to 1:4		RTU to 1:4								32 oz Trigger 1710001250032 1 gal Bottle 1710000650128 5 gal Pail 1700000150005 55 gal Drum 1700000150155
SIMPLE GREEN® d PRO 3 <ul style="list-style-type: none"> • One-step hospital-grade disinfectant, cleaner, deodorizer • Kills MRSA, HIV-1, Influenza A and more • Fresh herbal-pine scent 	1:64	1:64	1:64			1:64	1:64		1:64	1:64			1:64	32 oz Bottle 3310001230332 1 gal Bottle 3310000630301 5 gal Pail 3300000130305 55 gal Drum 3300000130355
SIMPLE GREEN® d PRO 5 <ul style="list-style-type: none"> • One-step disinfectant virucide, fungicide, mildewstat, cleaner and sanitizer • Blood-borne pathogen compliant disinfectant • Kills MRSA, HIV-1, Influenza A, Hep B & C, and more • No added color or scent 	1:64	1:64	1:64			1:64	1:64		1:64	1:64			1:64	32 oz Bottle 3410001230532 1 gal Bottle 3410000430501 5 gal Pail 3400000130505 55 gal Drum 3400000130555
• SANITIZING DILUTION >>>	1:128	1:128	1:128			1:128	1:128							
SIMPLE GREEN STAINLESS STEEL® ONE-STEP CLEANER & POLISH <ul style="list-style-type: none"> • Non-toxic and biodegradable • Non-petroleum, zero VOC's • Non-abrasive and non-flammable • Cleans and polishes, stainless steel, chrome, metal surfaces, and more 	RTU	RTU	RTU	RTU	RTU	RTU	RTU					X	X	32 oz Trigger 3510001218300
PROPORTIONERS <ul style="list-style-type: none"> • Various configurations available for multiple products and dilutions • Ensure proper mixing for specific applications • Save money by cutting material usage • Lockable wire racks also available 	X		X	X	X	X	X	X	X			X	X	1 Product, 1 dilution 0800000113391 1 Product, 4 dilutions 0800000113384 4 Product, 4 dilutions 0800000113390 5 Product, 5 dilutions 0800000113385
PARTS WASHERS <ul style="list-style-type: none"> • Corrosion resistant construction, longer lasting components • Heating elements—heat preset to 110°F • Ground fault interrupter 	1:3				1:3	1:3			1:3	1:3			1:3	30 gal Unit 0800000179130 60 gal Unit 0800000179260 80 gal Unit 0800000179180

DILUTION RATIO: The 1st number represents the amount of Simple Green product recommended. The 2nd number represents the amount of water.