

**PRODUCT SPECIFICATION**

**Printed:** 2/10/2014

**Catalog :** AC110

Glacial Acetic Acid, USP

**CAS# :** 64-19-7

**Formula :** C2H4O2

**Formula Weight :** 60.05

Test	Limit	
	Min.	Max.
ASSAY	99.5	100.5 %
CONGEALING TEMPERATURE	15.6 C°	--
NONVOLATILE RESIDUE (w/v)	--	0.005%
CHLORIDE (Cl)	--	TO PASS TEST
SULFATES (SO <sub>4</sub> )	--	TO PASS TEST
HEAVY METALS	--	5 PPM
READILY OXIDIZABLE SUBSTANCES	--	TO PASS TEST
IDENTIFICATION	--	TO PASS TEST
RETEST DATE		
RESIDUAL SOLVENTS	--	TO PASS TEST