

**PRODUCT SPECIFICATION**

**Printed:** 2/10/2014

**Catalog :** BE159

Benzyl Benzoate, USP

**CAS# :** 120-51-4

**Formula :** C<sub>14</sub>H<sub>12</sub>O<sub>2</sub>

**Formula Weight :** 212.24

**Test**

**Limit  
Min. Max.**

Test	Limit Min. Max.
ASSAY (C <sub>14</sub> H <sub>12</sub> O <sub>2</sub> )	99.0 - 100.5 %
SPECIFIC GRAVITY @ 25[dC	1.116 - 1.120
CONGEALING TEMPERATURE	18.0 C
REFRACTIVE INDEX @ 20[dC	1.568 - 1.570
ACIDITY	--TO PASS TEST
ALDEHYDE	-- 0.05 %
IDENTIFICATION	--TO PASS TEST
RETEST DATE	
RESIDUAL SOLVENTS	--TO PASS TEST