

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : HY115

Hydrogen Peroxide, 35 Percent Solution, FCC

CAS# : 7722-84-1

Formula : H2O2

Formula Weight : 34.01

Test

**Limit
Min. Max.**

		Limit
		Min. Max.
ASSAY (H ₂ O ₂)		35.0 % --
ACIDITY (asH ₂ SO ₄)		-- 0.03 %
IRON (Fe)		-- 0.5 MG/KG
LEAD (Pb)		-- 4 MG/KG
PHOSPHATE (PO ₄)		-- 0.005 %
RESIDUE ON EVAPORATION		-- 0.006 %
TIN (Sn)		-- 10 MG/KG
IDENTIFICATION		TO PASS TEST