

## PRODUCT SPECIFICATION

**Printed:** 2/10/2014

Page 1 of 1

**Catalog :** PR130

Propylene Glycol, USP

**CAS# :** 57-55-6

**Formula :** C<sub>3</sub>H<sub>8</sub>O<sub>2</sub>

**Formula Weight :** 76.10

**Test**

**Limit**  
**Min.    Max.**

Test	Limit Min.    Max.
ASSAY	99.5 %    --
SPECIFIC GRAVITY @ 25[dC	1.035 - 1.037
ACIDITY	-- TO PASS TEST
WATER	--    0.2 %
RESIDUE ON IGNITION	--    0.007 %
CHLORIDE (Cl)	--    0.007 %
SULFATES (SO <sub>4</sub> )	--    0.006 %
HEAVY METALS (as Pb)	--    0.0005 %
IDENTIFICATION	-- TO PASS TEST
CERTIFIED KOSHER	
EXPIRATION DATE	
RESIDUAL SOLVENTS	-- TO PASS TEST