

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : SO204

Sodium Sulfate, Anhydrous, USP, EP, BP

CAS# : 7757-82-6

Formula : Na₂SO₄

Formula Weight : 142.04

Test	Limit	
	Min.	Max.
ASSAY (DRIED BASIS)	99.0 - 101.0%	
ACIDITY / ALKALINITY	TO PASS TEST	
LOSS ON DRYING	--	0.5%
CHLORIDE (Cl)	--	0.02%
HEAVY METALS (as Pb)	--	0.001%
APPEARANCE OF SOLUTION	TO PASS TEST	
RESIDUAL SOLVENTS	TO PASS TEST	
IDENTIFICATION	TO PASS TEST	
EXPIRATION DATE		