

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : S1519

Tris(hydroxymethyl)aminomethane, Crystal, Reagent, ACS

CAS# : 77-86-1

Formula : C₄H₁₁NO₃

Formula Weight : 121.14

Test

Limit
Min. Max.

	99.8 - 100.1 %
	-- TO PASS TEST
	-- 2 %
	-- 0.005 %
	-- 5 PPM
	-- 5 PPM
ASSAY (DRIED BASIS)	99.8 - 100.1 %
ABSORBANCE	-- TO PASS TEST
WATER	-- 2 %
INSOLUBLE MATTER	-- 0.005 %
HEAVY METALS (as Pb)	-- 5 PPM
IRON (Fe)	-- 5 PPM
EXPIRATION DATE	