





PolyTac® LED HP Tactical Light

FL 1 STANDARD	POLYTAC LED HP
	150 LUMENS
	3h
	245m
	15,000cd



Material/Lens High impact super tough nylon polymer for exceptional durability and a sure grip. All openings o-ring sealed for weather resistance. Available in black or yellow. Unbreakable polycarbonate lens with scratch-resistant coating, o-ring sealed

Dims/Weight Length: 5.65 in. (14.35 cm) Major Diameter: 1.70 in. (4.32 cm) Body Diameter: 1.00 in. (2.54 cm)
4.4 oz (125 grams)

Light Source C4® LED technology, impervious to shock with a 50,000 hour lifetime
LED Solid State Power Regulation provides maximum light output throughout battery life

Switch Push-button tail switch for one-handed operation

Battery Two 3V CR123A lithium batteries (included)

- Features**
- Ideal for down-range applications requiring optimal beam distance
 - High-candela beam
 - Sheds a bright peripheral beam
 - IPX7 rated design; waterproof to 1 meter for 30 minutes

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. **THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW.** You may have other specific legal rights which vary by jurisdiction.



Item	UPC	Part #
PolyTac LED HP with lithium batteries - Black	080926-88860-9	88860
PolyTac LED HP with lithium batteries - Yellow	080926-88863-0	88863
Rubber industrial hard hat strap	080926-99075-3	99075
Lithium batteries (2) Pack	080926-85175-7	85175
Lithium batteries (12) Pack	080926-85177-1	85177
Lithium batteries (400) Pack	080926-85179-5	85179
Lithium batteries (6) Pack	080926-85180-1	85180

