





# Stinger® LED Rechargeable Flashlight

FL1 STANDARD	HIGH	MEDIUM	LOW
	<b>350</b> LUMENS	<b>175</b> LUMENS	<b>85</b> LUMENS
	<b>2h</b>	<b>3h 45min</b>	<b>7h 15min</b>
	<b>310m</b>	<b>219m</b>	<b>155m</b>
	<b>24,000cd</b>	<b>12,000cd</b>	<b>6,000 cd</b>

Strobe runs for 5.5 hours



Designed for the broadest range of lighting needs at the best value.

**Material/ Lens** 6000 series machined aircraft aluminum with non-slip rubberized comfort grip and anti-roll rubber ring. Unbreakable polycarbonate lens with scratch-resistant coating

**Dims/Weight** Length: 8.41 in. (21.36 cm) Major Diameter: 1.62 in. (4.11 cm); Body Diameter: 1.17 in. (2.97 cm) 12.4 oz (352 grams)

**Light Source** C4® LED technology, shock-proof with a 50,000 hour lifetime. Deep-dish parabolic reflector produces a concentrated beam with optimum peripheral illumination. Regulated run time provides consistent performance throughout battery life

**Switch** Multi-function, easy access push-button switch designed for extremely long life; tested at 1 million actuations. Access high, medium, low and strobe

**Battery** 3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times  
3-cell, 3.6 Volt Ni-MH sub-C battery, rechargeable up to 1000 times offered in 230V AC and 12V DC systems

**Charging** Ten hours to fully recharge on 100V, 120V, 230V or 240V AC, or 12V DC, 2.5-hour fast charger or PiggyBack® charger model available

**Features**

- Anti-roll ring included
- LED charge-continuity indicator, compact
- IPX4 Rated for water resistant operation
- 1 meter impact resistance tested
- Snap-in charger holder that mounts in any position
- Serialized for positive identification

**Approvals** Most models meet applicable European Community Directives

**Warranty** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
Steady Charge AC/DC - 2 Holders		
Stinger LED with 230V	080926-75725-7	75725
Stinger LED with 120V	080926-75713-4	75713
AC Only		
Stinger LED with 230V	080926-75724-0	75724
Stinger LED with 240V	080926-75728-8	75728
Stinger LED with 120V	080926-75711-0	75711
Stinger LED with 100V	080926-75717-2	75717
DC Only		
Stinger LED with DC	080926-75712-7	75712
Steady Charge AC/DC PiggyBack		
Stinger LED with 120V	080926-75732-5	75732

Item	UPC	Part #
AC/DC Fast Charger - 2 Holders		
Stinger LED with 230V	080926-75727-1	75727
Stinger LED with 120V	080926-75735-6	75735
AC Fast Charger		
Stinger LED with 230V	080926-75726-4	75726
Stinger LED with 100V	080926-75719-6	75719
(WITHOUT CHARGER)		
Stinger LED	080926-75710-3	75710
<i>See reverse for additional part numbers</i>		



Item Description - NiMH Configurations	UPC	Part #
Stinger LED 230V AC/DC - 2 Holders NiMH Battery	080926-75962-6	75962
Stinger LED 230V AC NiMH Battery	080926-75961-9	75961
Stinger LED 12V DC NiMH Battery	080926-75753-0	75753
Stinger LED 230V AC/DC Fast Charge 2 Holders NiMH Battery	080926-75964-0	75964
Stinger LED 230V AC Fast Charge NiMH Battery	080926-75963-3	75963
Stinger LED 12V DC Fast Charge NiMH Battery	080926-75754-7	75754
Stinger LED - (WITHOUT CHARGER) NiMH Battery	080926-75960-2	75960

Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
100V AC charge cord	080926-22666-1	22666
230V AC charge cord	080926-22664-7	22664
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
5 Unit Bank Charger, 100V	080926-75700-4	75700
5 unit bank charger 100V	080926-75701-1	75701
Flip Lens IR	080926-75027-2	75027
Flip Lens Red	080926-75115-6	75115
Flip Lens Blue	080926-75116-3	75116
Flip Lens Green	080926-75117-0	75117
C4 LED Upgrade kit	080926-75768-4	75768
Battery Stick (NiCd)	080926-75175-0	75175
Battery Stick (NiMH)	080926-75375-4	75375
PiggyBack® Charger Holder - Steady Charger & Battery	080926-75275-7	75275
PiggyBack® Charger Holder Fast Charge & Battery	080926-75276-4	75276
Safety Wand Blue	080926-75902-2	75902
Safety Wand Red	080926-75903-9	75903
Safety Wand Yellow	080926-75904-6	75904
Safety Wand White	080926-75908-4	75908
Safety Wand Glow in the Dark	080926-75913-8	75913
Stinger DS LED Tail Cap Switch - Fits Stinger LED Model flashlights with serial #034389 and later	080926-75851-3	75851
Ring Holder	080926-75906-0	75906
Holster	080926-75927-5	75927
Loop holster	080926-75928-8	75928
Leather holster: Plain - Stinger LED/PolyStinger LED Series	080926-75133-0	75133
Leather holster: Basket Weave - Stinger LED/PolyStinger LED Series	080926-75134-7	75134



**STREAMLIGHT**



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax  
 www.streamlight.com ©Streamlight, Inc. Stinger LED 10/12