

Nes[®] Sets

Universal Thread Repair Tool

Nes1015 Combination External 4-19 mm $\frac{5}{32}$ " - $\frac{3}{4}$ " Internal 8-16 mm $\frac{5}{16}$ " - $\frac{5}{8}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1015	01015	Nes External 1A Nes Internal 21 Nes Internal 22	RK 1 60° RK 21 60° RK 22 60°	inch	10 $\frac{1}{16}$ "	6"	1 $\frac{13}{16}$ "	1.7	800
				mm	256	152	46		



Nes1017 Combination External 4-19 mm $\frac{5}{32}$ " - $\frac{3}{4}$ " Internal 8-20 mm $\frac{5}{16}$ " - $1\frac{1}{16}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1017	01017	Nes External 1A Nes Internal 21 Nes Internal 22 Nes Internal 23	RK 1 60° RK 21 60° RK 22 60° RK 23 60°	inch	10 $\frac{1}{16}$ "	6"	1 $\frac{13}{16}$ "	2.2	1000
				mm	256	152	46		



Nes1025 Combination External 4-38 mm $\frac{5}{32}$ " - $1\frac{1}{2}$ " Internal 8-32 mm $\frac{5}{16}$ " - $1\frac{1}{4}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1025	01025	Nes External 1A Nes External 2 Nes Internal 21 Nes Internal 22 Nes Internal 23 Nes Internal 24	RK 1 60° RK 2 60° RK 21 60° RK 22 60° RK 23 60° RK 24 60°	inch	10 $\frac{13}{16}$ "	8 $\frac{1}{16}$ "	1 $\frac{15}{16}$ "	4.9	2200
				mm	275	205	50		

