

U6400 Viking Journeyman 300D Tri-zone 3-in-1 Hi-vis Safety Jacket and Pants

Available in Orange & Lime Green Color

Available in Size S - 4XL



WHY U6400?

- Premium 300 Denier Polyester/PVC backing fabric provides good resistance against abrasions, punctures, rips and snags
- 260 GSM inner fleece with shell jacket good for up to -20°C/-4°F
- Bib pants are 60 GSM polyfill insulated, lightweight and fully lined providing protection against cold weather good for down to -20°C/-4°F without puffiness
- Double sewn, taped and heat sealed seams to maximize waterproofness

IDEAL FOR

- Traffic flaggers
- Construction
- Truckers
- Transit authorities
- Waste management

THE STANDARDS:

- 2" **3M Scotchlite**™ Reflective Material in 4" contrasting tape meets WCB/Worksafe/DOT configuration
- Fully compliant with ANSI/ISEA 107-2010 Class 3 Level 2 on the jacket; Class E Level 2 on the bib pants
- Fully compliant with CSA Z96-09 Class 2, Level 2 and becomes Class 3 in combination with right model arm and leg bands



U6400JG

1

Dual chest straps for ID badge/cell/radio and Cell/radio pouch pocket on left side of chest

2

Inner fleece liner is included & fully lined for comfort

3

Pit zippers provide breathability

4

Two sealed outside pockets



1

Heavy duty elastic suspenders with quick release buckle

2

Detachable bib with inner zippered storage pocket

3

Elasticized waist with Velcro fly access

4

Inner pants are fully lined for comfort

5

13" Adjustable cuffs for easy boot access

U6400PG

Available in:



U6400JO

1

Inner liner has 2" **Vibrance**™ reflective material

2

260 GSM premium polyester inner safety jacket with detachable hood



Inner fleece liner

