

Cutting-Edge Brushes in 3 Unique Blends



Cat. No.	UPC 0-71497-	Size	Description	Length	Thick	Pack	Cubic Ft. Per Pack	Pounds Per Pack
4187	14806-3	2"	Firm Shortcut®	2 7/16"	1/2"	6	.072	1.16
	14807-0	2½"	angle sash	2 11/16"	5/8"	6	.124	1.92
	16809-2	3"		3 3/16"	11/16"	6	.168	2.67
4174	11992-6	1½"	Firm Lindbeck®	2 7/16"	1/2"	6	.088	1.04
	15004-2	2"	angle sash	2 11/16"	9/16"	6	.102	1.39
	15005-9	2½"		2 15/16"	5/8"	6	.146	1.98
	15006-6	3"		3 3/16"	11/16"	6	.178	2.55
	13945-0	3½"		3 3/8"	11/16"	6	.225	2.88
4184	13748-7	2"	Firm Shergrip®	2 11/16"	9/16"	6	.102	1.54
	13749-4	2½"	Lindbeck	2 15/16"	5/8"	6	.146	2.10
	13750-0	3"	angle sash	3 3/16"	11/16"	6	.189	2.80
4181	11993-3	1"	Firm Willow®	2 3/16"	5/16"	6	.062	.62
	11994-0	1½"	thin angle sash	2 3/16"	3/8"	6	.088	.92
	18424-5	2"		2 7/16"	7/16"	6	.102	1.12
	18425-2	2½"		2 11/16"	1/2"	6	.146	1.65
	18426-9	3"		2 15/16"	1/2"	6	.146	1.87
	14349-5	3½"		3 3/16"	9/16"	6	.178	2.38
4189	16810-8	3"	Firm Mink™	3 3/16"	11/16"	6	.168	2.80
			Shortcut flat sash					
4175	12000-7	1½"	Firm Mink	2 7/16"	1/2"	6	.088	1.06
	15054-7	2"	flat sash	2 11/16"	9/16"	6	.102	1.42
	15055-4	2½"		2 15/16"	5/8"	6	.146	1.91
	15056-1	3"		3 3/16"	11/16"	6	.189	2.49
4195	13782-1	2"	Firm Philly™	2 15/16"	3/4"	6	.146	1.87
	15115-5	2½"	flat sash	3 3/16"	3/4"	6	.189	2.38
4177	18445-0	2½"	Firm Lindbeck	2 15/16"	5/8"	6	.146	1.76
	14351-8	3"	Sable™ angle varnish	3 3/16"	11/16"	6	.146	2.38
4176	14265-8	1"	Firm Sable	2 3/16"	7/16"	6	.052	.61
	14266-5	1½"	varnish	2 7/16"	1/2"	6	.088	1.00
	13753-1	2"		2 11/16"	9/16"	6	.102	1.32
	13754-8	2½"		2 15/16"	5/8"	6	.146	1.78
	15096-7	3"		3 3/16"	11/16"	6	.146	2.27
	14348-8	3½"		3 7/16"	11/16"	6	.191	2.72
4183	14909-1	2"	Firm Lynx™	2 11/16"	9/16"	6	.102	1.26
	14910-7	2½"	dowel-handle	2 15/16"	5/8"	6	.146	1.70
	14911-4	3"	varnish	3 3/16"	11/16"	6	.146	2.22
	17673-8	3½"		3 3/16"	11/16"	6	.178	2.50
	14912-1	4"		3 11/16"	7/8"	6	.273	3.84
4179	14352-5	2½"	Firm Shasta®	3 3/16"	25/32"	6	.146	2.06
	18410-8	3½"	varnish	3 7/16"	25/32"	6	.178	2.58
	14353-2	3½"		3 11/16"	25/32"	6	.225	2.96
4180	18437-5	3½"	Firm Lindbeck	3 7/16"	7/8"	6	.225	3.13
			Jaguar® angle wall					
4173	15146-9	3"	Firm Jaguar wall	3 7/16"	7/8"	6	.189	2.85
	15147-6	3½"		3 11/16"	7/8"	6	.225	3.21
	15148-3	4"		3 15/16"	7/8"	6	.273	3.79
4185	13751-7	3"	Firm Shergrip	3 7/16"	7/8"	6	.189	2.94
			Jaguar wall					
4182	14922-0	2½"	Firm Bengal™	3 7/16"	1"	6	.148	2.48
	13360-1	3"	wall	3 11/16"	1"	6	.189	2.96
	13361-8	4"		3 15/16"	1"	6	.273	3.96

Featured on brushes indicated with **maroon** text in the chart, Wooster's patented Shergrip® handle provides a comfortable nonslip grip, even on hot days. The elastomeric material has a unique soft feel, resists cracking or peeling, and is very easy to clean.



One of Wooster's many innovations in brushmaking hit the market in 1985. Compared to the industry's other natural and synthetic filament brushes, the new Ultra/Pro brand featured shorter filaments to offer better control and increased production! Today, Ultra/Pro still sets the gold standard in performance. Wooster's exclusive "pencil point" tipping virtually eliminates brushmarks and delivers one of the smoothest strokes in the business. Available in soft, firm, and extra-firm blends, all three provide excellent paint pickup and release for the fastest results.



Ultra/Pro® Soft



These brushes feature a feather-soft blend with a fine touch. Made from top-quality nylon, Ultra/Pro Soft is designed for fine finish painting with clears, stains, and low viscosity paints or primers. The exceptional flex and softness provide superior performance in low humidity and cooler temperatures, great for interiors, and 100% nylon cleans up easily after the job. Look for the purple filament and the purple stamp on the handle.

For That Unique Soft Touch

- Feather-soft blend with extra flex
- Made of 100% purple nylon
- Recommended for use with fast-drying and low viscosity coatings
- Provides the smoothest finish for mirror-like results

•• **“No-Brushmarks Finish”**

•• **Extra Flex**



Ultra/Pro® Extra-Firm



Able to cut a sharp line even in hot or humid conditions, Ultra/Pro Extra-Firm is the perfect choice for all thick or fast-drying paints and primers. It excels during exterior use. Made from 100% nylon and featuring an exclusive Wooster filament called NylonPlus™, it maintains rigidity, resists wear, and cleans much more easily than brushes that use polyester to achieve extra stiffness. Look for the purple and black filament and the teal stamp on the handle.

For That Unique Extra-Firm Touch

- Extra-firm blend for solid response
- Made with purple NylonPlus™ filament and purple and black nylon
- Recommended for use with thick or low VOC coatings
- Provides superior stiffness retention and control for reliable results

•• **Maintains Stiffness**

•• **Excellent Cut-In Control**



Cat. No.	UPC 0-71497-	Size	Description	Length	Thick	Pack	Cubic Ft. Per Pack	Pounds Per Pack
4170	11995-7	1½"	Soft Lindbeck® angle sash	2 7/16"	1/2"	6	.088	1.04
	11996-4	2		2 11/16	9/16	6	.102	1.42
	11997-1	2½		2 15/16	5/8	6	.146	2.00
	15236-7	3		3 3/16	11/16	6	.178	2.57
	13944-3	3½		3 3/8	11/16	6	.178	3.00
4169	18406-1	3"	Soft Sable™ varnish	3 3/16"	11/16"	6	.146	2.25
4166	15049-3	3"	Soft Lynx™ dowel-handle varnish	3 3/16"	11/16"	6	.146	2.08
4171	15356-2	3"	Soft Jaguar® wall	3 7/16"	7/8"	6	.189	2.78

Cat. No.	UPC 0-71497-	Size	Description	Length	Thick	Pack	Cubic Ft. Per Pack	Pounds Per Pack
4153	14374-7	1½"	Extra-Firm Lindbeck® angle sash	2 7/16"	1/2"	6	.088	1.06
	14375-4	2		2 11/16	9/16	6	.102	1.42
	14376-1	2½		2 15/16	5/8	6	.146	2.00
	14377-8	3		3 3/16	11/16	6	.178	2.50
4151	16808-5	3"	Extra-Firm Shortcut® angle sash	3 3/16"	11/16"	6	.168	2.61
4157	14388-4	3"	Extra-Firm Sable™ varnish	3 3/16"	11/16"	6	.146	2.34
4159	15834-5	3"	Extra-Firm semioval	3 11/16"	1 1/8"	6	.215	2.70
4156	14385-3	3"	Extra-Firm Jaguar® wall	3 7/16"	7/8"	6	.189	2.92
	14387-7	4		3 15/16	7/8	6	.273	3.83

Ultra/Pro® Firm

Ultra high production makes Ultra/Pro Firm the best-selling blend and a favorite for over 25 years. Featuring a mix of nylon and polyester, it's truly an all-purpose professional brush for use in acrylics, latex, or enamels, indoors and out. With fantastic coverage and masterful cut-in control, it saves painters time wherever a firm brush is needed. Look for the purple and sable brown filament and the maroon stamp on the handle.

For That Unique Firm Touch

- Top-selling firm blend for balanced flex
- Made of purple nylon/sable polyester
- Recommended for use with medium-weight coatings, indoors or out
- Provides excellent coverage for all-purpose painting

•• **Good Glide, No Drag**

•• **Professional Coverage**

See brush chart on back page



Soft



Firm



Extra-Firm