

If our 6½” Mini-Koter rollers are the hot dogs, these are the cocktail franks.

The new 4” Mini-Koter program from Wooster stuffs a lot of performance into a little roller. All have closed ends for painting corners! These minis are also great for cabinets, railings, furniture, and trim. The small size easily reaches behind radiators or into other narrow spaces. Trilingual, color-coded bags have headers for better merchandising on peghooks. The 4” Mini-Koter program is an appetizing way to complete your trim tool menu.



R226 High-Capacity Yarn picks up a lot of paint to save trips to the bucket. Use this mop-like white fabric with all flat paints, stains, and sizings.



R227 Mohair Blend™ white fabric combines shed-resistant mohair with non-matting polyester. Use with enamels, varnishes, and polyurethanes.

R228 Pro Foam™ offers high capacity and density along with a lint-free finish. Use this charcoal-colored foam with varnishes, enamels, and all paints.

4” MINI-KOTER ROLLERS Best-quality fabrics offer excellent paint pickup and a very smooth finish. Closed ends save time by painting inside corners—no brush cut-in required. These metric rollers are for use only with the Wooster Mini-Koter 4” roller frame, R012-4. Packed two per bag.

Cat. No.	UPC 0-71497-	Description	Size	Nap	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
R227	14473-7	Mohair Blend	4”	1/4”	12	.185	1.14
R226	14472-0	High-Capacity Yarn	4”		12	.185	1.22
R228	14474-4	Pro Foam	4”		12	.185	1.08

4” MINI-KOTER FRAME Galvanized 6mm wire shank. Blue plastic grip, threaded for extension pole use. Overall 12” length. This frame is made exclusively for the closed-end 4” Mini-Koter rollers.

Cat. No.	UPC 0-71497-	Description	Size	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
R012	14481-2	4” Mini-Koter frame	4”	12	.143	3.00

Remember, you need the R012 frame for the rollers (even more than a hot dog needs ketchup)!

