MAN & MACHINE

D Cool

Sealed Backlit Typing Solution





Featuring



Wash Without Disconnecting



Withstands 1:10 Bleach Solution




Good Tactile Feel Single or Double Gloved




Exceptional Value

D Cool Keyboard Details

MAN & MACHINE









Features

- · Sealed, waterproof, immersible
- · Locking keys lock for workstation disinfection
- Cleans with 1-10 bleach solution or any EPAcertified disinfectant
- · Good tactile feedback
- No moving parts, no mechanical failure
- · Standard key pitch
- · 1-year ltd. warranty

Specifications

- IP 67
- · Color: White/Black
- Size: 15 x 5.1 x .4 in (380 x 130 x 11 mm)
- Weight: 1.28 lbs (580 g)
- Cable length: 70.8 in (1.8 m)
- Storage temperature: -4° to 158° F (-20° to 70° C)
- Operating temperature: 32° to 158° F (0° 70° C)
- Power consumption: 5V/26mA

150mA (backlighted)

- Platform Win, MAC
- · Connection USB
- · Number of keys 110
- · Switch rating 2 million

Color Choices





info@mmimd.com www.man-machine.com (301) 341-4900



