

HDMI SWITCHER 4 INPUTS X 2 OUTPUTS

OE-HDMIMX2



SUPPORTS RESOLUTIONS UP TO 4K@60 4:4:4 AND HDCP 2.2 COMPATIBILITY. SUPPORTS DIGITAL AND ANALOG AUDIO DE-EMBEDDING, IR CONTROL AND RS232 CONTROL.

SPECIFICATIONS:

Technical

- Input/Output Port:
 - 4 x HDMI IN, 2 x HDMI OUT, 1 x AUDIO OUT, 1 x S/PDIF OUT, 1 x RS232, 1 x DC 5V IN
- Resolution Supported:

VESA: 800x600⁸, 1024x768⁸, 1280x768⁸, 1280x800⁸, 1280x960⁸, 1280x1024⁸,1360x768⁸, 1366x768⁸, 1440x900⁸, 1600x900⁸, 1600x1200⁸, 1680x1050⁸, 1920x1200⁸

SMPTE: 720x576P⁶, 1280x720P^{6,7,8}, 1920x1080P^{2,5,6,7,8}, 3840x2160^{2,3,5,6,8}, 4096x2160^{2,3,5,6,8}

(1 = at 23.98 Hz, 2 = at 24 Hz, 3 = at 25 Hz, 4 = at 29.97 Hz, 5 = at 30 Hz, 6 = at 50 Hz, 7 = at 59.94 Hz, 8 = at 60 Hz, 9 = at 75 Hz)

- Maximum Data Rate: 18Gbps
- Maximum Pixel Clock: 600MHz
- Audio Format:

HDMI IN/OUT: Fully supports audio formats in HDMI 2.0 specification, including PCM 2.0/5.1/7.1, Dolby TrueHD, Dolby Atmos, DTSHD Master Audio and DTS:X AUDIO OUT: Only support PCM 2.0; S/PDIF OUT: Support PCM 2.0/5.1, Dolby digital and DTS up to 5.1 Channel.

Warranty: 2 years

For more information please call 1-833-574-9124 or email AVARRO@adiglobal.com

To learn more about AVARRO products visit avarro.adiglobaldistribution.us


PART#: 0E-HDMIMX2UPC: 840049305779

General

- Operating Temperature:
 0°C to 45°C (32°F to 113°F)
- Storage Temperature:
 -20°C to 70°C (-4°F to 158°F)
- Humidity: 10% to 90%, non-condensing
- ESD Protection:
 ±8kV (Air-gap discharge)/
 ±4kV (Contact discharge)
- Surge Protection: Voltage: ±1 kV
- Power Supply: DC 5V 1A
- Power Consumption (max): 3.3W
- Device Dimension (Transmitter / Receiver):
 22.0 cm x 2.1 cm x 10.02cm/8.66" x 0.83" x 3.94"
- Product Weight (Transmitter/Receiver): 0.48kg/1.06lbs



TECHNICAL DRAWING OE-HDMIMX2



For more information please call 1-833-574-9124 or email AVARRO@adiglobal.com

To learn more about AVARRO products visit avarro.adiglobaldistribution.us