# Model #: TRAVELER100BT

## 2 AC outlets, direct plug-in surge suppressor with single line Ethernet or modem/fax surge protection

### Highlights

- 2 outlets/Direct plug-in
- 1050 joule rating
- Retractable plug
- Single line Ethernet or modem/fax surge protection
- $50,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

## Description

Tripp Lite's portable TRAVELER100BT surge suppressor offers complete AC and Ethernet or phone line surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact portable housing weighing less than 4 ounces neatly fits into laptop travel cases. Retractable plug prevents scratching of expensive portable electronics. Set of RJ45 Ethernet or telephone line suppression jacks protect network lines or dialup and DSL modem lines. TRAVELER100BT offers 2 total outlets in a space saving direct plug-in format and diagnostic LEDs to warn of wiring problems and suppressor damage. $50,000  Ultimate Lifetime Insurance (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 2 NEMA5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Direct plug-in suppressor hangs off of standard wall socket

SUPPRESSION: AC: 140V RMS Clamping/1050 joules/330V UL1449 Let-through Rating Phone: Single Ethernet or telephone line surge suppression (RJ45 jacks, 2 wire, 1 line)

Applications

- Ideal for use with laptops, electronic notepads, personal organizers and other portable electronic devices.

Package Includes

- TRAVELER100BT Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

## Features

- 1050 joules AC surge suppression shields equipment from the strongest surges and line noise
- 2 AC outlets with room for 2 transformer plugs without blocking outlets covers computer and one peripheral
- Ethernet or phone line surge suppression protects network lines or dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ45 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Exceeds IEEE 587 category A & B surge suppression specifications
- Extra-small portable housing weighing less than 4 ounces neatly fits into laptop travel cases - retractable input plug prevents scratching of

laptops and other devices
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- UL1449 Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- $50,000 Ultimate Lifetime Insurance (USA and Canada Only)

## Specifications

| OVERVIEW | |
| --- | --- |
| **Intended Application** | Home/Office, Travel |
| **OUTPUT** | |
| **Frequency compatibility** | 50 / 60 Hz |
| **Output watts** | 1800 |
| **Circuit Breaker (amps)** | 15 |
| **Outlet quantity / type** | 2 NEMA 5-15R |
| **Transformer accommodation** | Supports up to 2 large transformer plug accessories without covering remaining outlets |
| **INPUT** | |
| **Recommended Electrical Service** | 120V (110-125V) |
| **Input connection type** | NEMA 5-15P with retractable input prongs |
| **Input cord length details** | Direct plug-in |
| **Voltage compatibility (VAC)** | 120 |
| **Maximum Surge Amps** | 30000 |
| **LEDS ALARMS & SWITCHES** | |
| **Diagnostic LEDs** | Two built-in LEDs confirm suppressor "protection present" (green) and outlet "grounded" (red) status |
| **SURGE / NOISE SUPPRESSION** | |
| **AC suppression joule rating** | 1050 |
| **AC suppression response time** | < 1 ns |
| **Protection modes** | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| **Clamping voltage (RMS)** | 150 |
| **UL1449 let through rating** | 330V - UL Verified |
| **DATALINE SURGE SUPPRESSION** | |
| **Telephone/DSL Protection** | Yes |
| **Telephone/DSL Protection Details** | 1 line |
| **Cable (Coax) Protection** | No |
| **Network (Ethernet) Protection** | Yes |
| **PHYSICAL** | |
| **Shipping weight (lbs)** | 0.4 |

| | |
|---|---|
| Shipping weight (kg) | 0.2 |
| Unit Dimensions (HWD/in) | 3.5 x 2.5 x 1.75 |
| Unit Dimensions (HWD/cm) | 8.9 x 6.4 x 4.4 |
| Shipping Dimensions (HWD/in) | 4 x 4 x 1.8 |
| Shipping Dimensions (HWD/cm) | 10.2 x 10.2 x 4.6 |
| Unit weight (lbs) | 0.3 |
| Unit weight (kg) | 0.15 |
| Material of construction | Plastic |
| Style | Direct Plug-in |
| Form factors supported | Direct plug-in connection enables mounting to any AC wall receptacle |

**SPECIAL FEATURES**

| | |
|---|---|
| Appearance | Ultra-compact, portable suppressor with retractable input plug fits easily in carrying case for laptops and other portable electronics |

**CERTIFICATIONS**

| | |
|---|---|
| UL1449 3rd Edition (AC Suppression) | UL1449 |
| NOM (Mexico) | NOM |
| UL1363 (Power Tap) | UL1363 |
| UL497A (Communications) | UL497A |
| FCC Part 68 (Communications) | FCC Part 68 |
| cUL / CSA (Canada) | cUL |
| Industry Canada (Communications) | Industry Canada |
| Approvals | Exceeds IEEE 587 category A&B specifications |

**WARRANTY**

| | |
|---|---|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | $50,000 Ultimate Lifetime Insurance |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at
www.tripplite.com/en/products/model.cfm?txtModelID=3055.