

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Black, 5-Pack

MODEL NUMBER: P004-002-5









Computer power extension cords connect 2 devices with C13/C14 power connectors or extend your existing power connection by 2 ft.

Features

C14-to-C13 Power Cables Connect Computers, Printers, Servers and Other EquipmentThis package of five IEC-320-C14 to IEC-320-C13 cables is designed for small data center, office workstation and other lower-amp applications. These C14 male to C13 female cords can be used to power computers, servers and monitors; attach routers and drives to a UPS system or PDU; or extend existing connections up to 2-ft. (0.61 m). The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Add 2-ft. (0.61 m) to your existing connection to provide more flexibility in placing devices
- C13-to-C14 PDU-style extension cords are ideal replacements for worn-out or missing cable

Applications

- Connect devices like computers, servers and routers to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend existing power connections up to 2-ft. (0.61 m) to more easily place devices or reach a power source near your workstation
- Provide high-quality replacements for worn-out or missing power cords

Package Includes

(5) C14 Male to C13 Female
Power Cables, 2-ft. (0.61 m),
Black

Specifications

OVERVIEW	
UPC Code	037332142863
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America



PRODUCT OVERVIEW		
Product Overview	5-Pack IEC-320-C14 to IEC-320-C13 Power Cables	
INPUT		
Maximum Input Amps	10	
Voltage Compatibility (VAC)	100-250	
PHYSICAL		
Color	Black	
Number of Conductors	3	
Wire Gauge (AWG)	18	
Wire Gauge (OD - mm²)	0.82	
Cable Length (ft.)	2	
Cable Length (m)	0.6	
Power Cord Jacket Type	SJT	
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27	
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50	
Shipping Weight (kg)	0.50	
Shipping Weight (lbs.)	1.10	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14	
Side B - Connector 1	IEC-320-C13	
SPECIAL FEATURES		
High Voltage	Yes	
Locking Plug	No	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies