

S CD8371-HNTV S CD8371-HNVF2

Corner Dome Network Camera



3MP · WDR Pro · SNV · 940nm IR · IK10+ · IP66 · Anti-Ligature · Anti-Grip

VIVOTEK's CD8371-HNVF2/HNTV is a vandal-proof network camera specifically designed for prisons and correctional facilities. With up to 20 fps at 3-Megapixel resolution, 940nm IR illuminators, two-way audio, and available in either fixed lens (-HNVF2) or vari-focal (-HNTV), the CD8371-HNVF2/HNTV is the most feature rich prison cell surveillance camera available today. The CD8371-HNVF2/HNTV has an anti-ligature design to limit the possibilities of self inflicted harm or suicide, a required feature for environments like prisons, holding cells, psychiatric wards, mental hospitals, and correctional institutions

Along with having an anti-ligature design, the CD8371-HNVF2/HNTV is designed to cover a wide area. Designed to be installed in the upper corner of a cell, the CD8371-HNVF2/HNTV has both a wide angle horizontal FOV (up to 108°) and

vertical FOV (up to 79°) enabling full coverage of a rectangular cell. Both models lenses also have a 15° vertical tilt to enable vertical view adjustments where needed. WDR Pro is included enabling better image quality where variable lighting is a concern as well as SNV technology to produce high-quality full-color surveillance under low-light conditions. These combined features, along with a built-in microphone, enable correctional officers, mental health evaluators, and prison guards to monitor all the activities of those under their supervision.

The CD8371-HNVF2/HNTV also supports the industry-standard H.264 compression technology, reducing file sizes and conserving network bandwidth. It also is ONVIF compliant, enabling integration with any existing Video Management Software or VIVOTEK's own VAST Central Management Software

Key Features

- · 3-Megapixel CMOS Sensor
- · 20 fps @ 2048x1536
- Anti-Ligature Design, Corner Dome Correctional Facility Camera
- Weather-proof IP66 rated and Vandal-proof IK10+ rated Housing
- Up to 108° Horizontal Field of View, Up to 79° Vertical Field of View
- · 15° Tilt Lens
- · Built-in Invisible 940nm IR Illuminators up to 10 Meters
- · WDR Pro (100dB) for Improved Visibility in High Contrast Lighting Environments
- · SNV (Supreme Night Visibility)
- · Smart Stream II to Optimize Bandwidth Efficiency
- \cdot 3D Noise Reduction for Low-light Conditions
- Shock Detection Advanced Tamper Detection if Camera is Attacked



The Anti-Ligature, Robust Design, Corner Dome Correctional Facility Camera

Technical Specifications

| Model | CD8371-HNTV: Vari-focal, Remote Focus CD8371-HNVF2: Fixed-focal | | Adjustable image size, quality and bit rate; Time stamp, text overlay, flip & mirror; Configurable brightness, |
|----------------------------------|--|------------------------|--|
| System Information | | Image Settings | contrast, saturation, sharpness, white balance, exposure control, gain, backlight |
| CPU | Multimedia SoC (System-on-Chip) | 1 | compensation, privacy masks; Scheduled profile settings, 3D noise reduction, video rotation |
| Flash | 128MB | Audio | Τοτατίοπ |
| RAM | 256MB | Audio | |
| Camera Features | | Audio Capability | Two-way audio |
| Image Sensor | 1/2.8" Progressive CMOS | Compression | G.711, G.726 |
| Maximum Resolution | 2048x1536 (3MP) | Interface | Built-in microphone External microphone input External line output |
| Lens Type | CD8371-HNTV: Vari-focal, Remote Focus CD8371-HNVF2: Fixed-focal | Effective Range | 5 Meters |
| Focal Length | CD8371-HNTV: f= 2.8 ~ 8 mm CD8371-HNVF2: f= 2.8 mm | Network | |
| Aperture | CD8371-HNTV: F1.6 | Users | Live viewing for up to 10 clients |
| | CD8371-HNVF2: F1.8 CD8371-HNTV: 51*~105* (Horizontal) 37~72* (Vertical) | Protocols | IPv4, IPv6, TCP/IP, HTTP, HTTPS, UPnP, RTSP/RTP/RTCP, IGMP, SMTP, FTP, DHCP, NTP, DNS, DDNS, PPPOE, CoS, QoS, SNMP, 802.1X, NTCIP, ARP, SSL, TLS |
| Field of View | 63°-140° (Diagonal) CD8371-HNVF2: 108° (Horizontal) 79° (Vertical) 137° (Diagonal) | Interface | 10Base-T/100 BaseTX Ethernet (RJ-45) *It is highly recommended to use standard Cat. 5e & Cat. 6 cables which are compliant with the 3P/ETL standard. |
| Shutter Time | 1/5 sec. to 1/32,000 sec. | ONVIF | Supported, specification available at www. onvif.org |
| WDR Technology | WDR Pro | Intelligent Video | |
| Day/Night | Removable IR-cut filter for day & night function | Video Motion Detection | Five-window video motion detection |
| Minimum Illumination | CD8371-HNTV: 0.01 Lux @ F1.6 (Color) < 0.01 Lux @ F1.6 (B/W) 0 Lux with IR illumination on CD8371-HNVF2: 0.01 Lux @ F1.8 (Color) < 0.01 Lux @ F1.8 (B/W) 0 Lux with IR illumination on | Alarm and Event | |
| | | Alarm Triggers | Motion detection, manual trigger, digital input, periodical trigger, system boot, recording notification, camera tampering detection, audio detection, shock detection |
| Tilt Range | 15° | Alarm Events | Event notification using HTTP, SMTP, FTP, NAS server and SD Card File upload via HTTP, SMTP, FTP, NAS server and SD card |
| Pan/Tilt/Zoom Functionalities | ePTZ: 48x digital zoom (4x on IE plug-in, 12x built in) | General | Server and SD Card |
| IR Illuminators | Built-in 940nm IR illuminators, effective up to 10 meters with Smart IR | Smart Focus System | Remote Focus (CD8371-HNTV) |
| On-board Storage | Slot type: MicroSD/SDHC/SDXC card slot Seamless Recording | Connectors | RJ-45 cable connector for Network/PoE connection Audio input |
| Video | | | Audio output (Optional) DC 12V power input (Optional) |
| Compression | H.264 & MJPEG | | AC 24V power input (Optional) Digital input*1 (Optional) Digital output*1 (Optional) |
| Maximum Frame Rate | 20 fps @ 2048x1536 | LED Indicator | Digital output*1 (Optional) |
| Maximum Streams | 3 simultaneous streams | LED HIGICALOI | System power and status indicator |
| S/N Ratio | 55dB | Power Input | DC 12V AC 24V IEEE 802.3af PoE Class 2 |
| Dynamic Range | 100dB | Power Consumption | Max. 6.2 W |
| , | Adjustable resolution, quality and | Dimensions | 226 x 221 x 112 mm |
| Video Streaming | constant bit rate control; Smart Stream II | חווופוואטווא | 220 X 221 X 112 IIIIII |

Technical Specifications

| Weight | CD8371-HNTV: 1537 g CD8371-HNVF2: 1522 g | | |
|-----------------------|---|--|--|
| Casing | Weather-proof IP66 rated housing Vandal-proof IK10+ rated metal housing | | |
| Safety Certifications | CE, LVD, FCC Class A, VCCI, C-Tick, UL | | |
| Operating Temperature | Starting Temperature: -10°C ~ 55°C (14°F ~ 131°F) Working Temperature: -10°C ~ 55°C (14°F ~ 131°F) | | |
| Warranty | 36 months | | |
| System Requirements | | | |
| Operating System | Microsoft Windows 8/7/Vista/XP/2000 | | |
| Web Browser | Mozilla Firefox 7~43 (streaming only) Internet Explorer 7/8/9/10/11 | | |
| Other Players | VLC: 1.1.11 or above Quicktime: 7 or above | | |

Others Quick installation guide, warranty card, alignment sticker, desiccant bag, screw driver, screws pack, I/O cable, mounting bracket

Dimensions



