## 8502SFO1V06

NEMA Contactor, Type S, nonreversing, Size 4, 135A, 1 phase, up to 100 kA, 2 pole, 480 VAC coil, open



## Main

Product Type	Contactor
Product Range	8502S
Contactor Type	Non-reversing

Complementary

Complementary		
NEMA Size	4	
Rated Current	135 A	
Number of Poles	2P	
Maximum Voltage Rating	600 V AC	
Phase	1 phase	
Horsepower Rating	Not rated	
SCCR	Circuit-breaker 225 A maximum, SCCR: 100 kA at 480 V AC Fuse J 200 A maximum, SCCR: 100 kA at 600 V AC Fuse T 200 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 200 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 200 A maximum, SCCR: 100 kA at 600 V AC	
Coil Voltage	480 V AC 60 Hz 440 V AC 50 Hz	
Control Circuit Type	Common control circuit	
Control Units	No control units	
Pilot Light	No indicator	
Auxiliary Contacts	Without	
Other Equipment	Fuse not supplied	
Terminal Type	Screw clamp terminals	
Height	8.19 in (208.03 mm)	
Width	6.00 in (152.40 mm)	
Depth	6.50 in (165.10 mm)	

## Environmental

Enclosure Type	Not rated (open device)
Certifications	UL listed file E78351 CCN NLDX CSA

## Ordering and shipping details

Category	21193 - 8502,36 SE,SF(NOT S*R,T,W)	
Discount Schedule	CP1	
GTIN	00785901831532	
Nbr. of units in pkg.	1	
Package weight(Lbs)	17.05 lb(US) (7.73 kg)	

Returnability	No
Country of origin	MX
Packing Units	
Package 1 Height	7.70 in (19.558 cm)
Package 1 width	8.80 in (22.352 cm)
Package 1 Length	14.40 in (36.576 cm)
Offer Sustainability	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
Contractual warranty	
Warranty	18 months