

USB 3.0 External Flash Multi Media Memory Card Reader - SDHC MicroSD

Product ID: FCREADMICRO3



The FCREADMICRO3 USB 3.0 Multi-media Card Reader offers quick access to the most popular flash card formats, from any computer with a USB port (optimal performance with 3.0, backward compatible with USB 2.0).

Suitable for quickly accessing memory cards of virtually any portable media device (e.g. digital cameras, MP3 players, etc.), this versatile media card reader supports the most popular card types, including:

- Secure Digital (SD)
- Multi-Media Card (MMC)
- Mini-SD, Micro-SD/SDHC (T-flash)
- SDHC
- SDXC
- RS-MMC
- Mobile-MMC and MMC-micro
- Memory Stick (MS)
- Memory Stick PRO (MS-PRO)
- MS Duo
- MS-PRO Duo
- Memory Stick XC
- Micro-MS (M2)

- MSPRO-HG Duo 8-bit mode.

An ideal Laptop or Desktop accessory, this pocket-sized memory card reader is lightweight, portable, and backed by a StarTech.com 2-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mobile users/travelers who need a compact and lightweight card reader small enough to fit in a pocket
- Photographers who need to regularly transfer files from their camera memory card to a computer
- Transferring files to and from a variety of portable devices, each using a different memory card format

Features

- High Speed USB 3.0 host interface with support for transfer rates up to 5 Gbps
- Support for Secure Digital (SD), MultiMedia Card (MMC), Mini-SD, Micro-SD/SDHC (T-flash), SDHC, SDXC, RS-MMC, Mobile-MMC and MMC-micro, Memory Stick (MS), Memory Stick PRO (MS-PRO), MS Duo, MS-PRO Duo, Memory Stick XC, Micro-MS (M2), and MSPRO-HG Duo 8-bit mode
- Ultra-compact and lightweight design
- Powered directly from the USB port
- Plug-and-Play and Hot-Swap compatible

Hardware

Warranty	2 Years
Interface	USB 3.0
Bus Type	USB 3.0
Chipset ID	Realtek - RTS5307

Performance

Maximum Data Transfer Rate	5 Gbit/s
Memory Media Type	microSDHC (Micro Secure Digital High Capacity) MS Duo, MS Pro Duo, MS Pro-HG Duo



Memory Stick

M2 (Memory Stick Micro)

Multi Media Card

RS-MMC (Reduced Size Multimedia Card)

SD/MMC (Secure Digital/Multimedia Card)

SDHC (Secure Digital High Capacity)

HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card)

SDXC (Secure Digital eXtended Capacity)

MSXC (Memory Stick eXtended Capacity)

MS Micro (Memory Stick Micro)

Connector(s)

Connector Type(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)
External Ports	SD / MMC Slot
	Memory Stick / Memory Stick Pro Slot
	MicroSD

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	< 80% R.H.

Physical Characteristics

Color	Black
Material	Plastic



Product Length	2.8 in [72 mm]
Product Width	0.9 in [23 mm]
Product Height	0.6 in [15 mm]
Weight of Product	0.5 oz [15 g]

Packaging Information

Package Length	6.9 in [17.5 cm]
Package Width	5.6 in [14.2 cm]
Package Height	1.3 in [32 mm]
Shipping (Package) Weight	3.7 oz [104 g]

What's in the Box

Included in Package	USB 3.0 Multi Media Memory Card Reader Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

